

7805R Coax - RG-174 Type

For more Information
please call

1-800-Belden1



Description:

RG-174 type, 24.5 AWG solid .020" bare copper conductor, foam HDPE insulation, Beldfoil® + tinned copper braid shield (93% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	24.5	Solid	BC - Bare Copper	.0195

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
FHDPE - Foam High Density Polyethylene	.060

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	93

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.110 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +75°C

UL Temperature Rating: 80°C

Bulk Cable Weight: 10 lbs/1000 ft.

Max. Recommended Pulling Tension: 20 lbs.

Min. Bend Radius (Install)/Minor Axis: 0.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMG

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	174/U
Series Type:	RF 100

Flame Test

UL Flame Test:	UL1666 Riser
CSA Flame Test:	FT4

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes - When supported by a messenger

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

50

Nom. Inductance:

Inductance (µH/ft)

.068

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

26.2

Nominal Velocity of Propagation:

VP (%)

73.5

Nominal Delay:

Delay (ns/ft)

1.38

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

27.3

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

9.3

Maximum VSWR:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Max. VSWR
		5	6000	1.25:1

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
30	3.5
50	4.6
150	8.0
220	9.6
450	14.0
900	20.2
1500	26.6
1800	29.5
2000	31.2

2500	35.4
3000	39.4
3500	43.0
4500	50.0
5800	59.0
6000	60.6

Nom. Power Rating:

Freq. (MHz)	Rating (W)
30	216
50	154
150	74
220	57
450	34
900	21
1500	14
1800	13
2000	12
2500	10
3000	9
3500	8
4500	7
5800	5
6000	5

Max. Operating Voltage - UL:

Voltage
300 V RMS

Notes (Overall)

Notes: 100% Sweep tested. 6 GHz. Max. Belden® The Wire in Wireless®

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7805R 008100	100 FT	1.700 LB	GRAY	E	RF100LL WIRELESS 50 OHM COAX
7805R 0081000	1,000 FT	10.000 LB	GRAY		RF100LL WIRELESS 50 OHM COAX
7805R 008500	500 FT	5.500 LB	GRAY		RF100LL WIRELESS 50 OHM COAX

Notes:

E = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'

Revision Number: 1 Revision Date: 09-30-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

