


## 6548PA Multi-Conductor - Pro Audio and Intercom Systems

For more Information  
please call

1-800-Belden1



### Description:

22 AWG BC cond, FEP insul, cond twisted into pairs and individually shielded w/Beldfoil® tape (alum side facing in), drain wire, multiple pairs cabled together, Fluorocopolymer (22 AWG) or Flamarest® (18 AWG) jkt, ripcord. Seq ftg marking every two ft.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
12	22	7x30	BC - Bare Copper	.029

#### Insulation

##### Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (in.)	Dia. (in.)
Teflon®	FEP - Fluorinated Ethylene Propylene	.010	.049

#### Inner Shield

##### Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

##### Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

#### Outer Shield

##### Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVDF - Fluorocopolymer	.017

Outer Jacket Ripcord: Yes

#### Overall Cable

Overall Nominal Diameter: 0.408 in.

#### Pair

##### Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown
7	Black & Orange
8	Red & White

9	Red & Green
10	Red & Blue
11	Red & Yellow
12	Red & Brown

**Pair Lay Length & Direction:**

Lay Length (in.)	Twists/ft. (twist/ft)
1.375	6.900

### Mechanical Characteristics (Overall)

<b>Operating Temperature Range:</b>	-20°C To +150°C
<b>UL Temperature Rating:</b>	75°C
<b>Bulk Cable Weight:</b>	116 lbs/1000 ft.
<b>Max. Recommended Pulling Tension:</b>	218.400 lbs.
<b>Min. Bend Radius (Install)/Minor Axis:</b>	4 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

<b>NEC/(UL) Specification:</b>	CMP
<b>NEC Articles:</b>	800
<b>CEC/C(UL) Specification:</b>	CMP
<b>EU CE Mark:</b>	Yes
<b>EU Directive 2000/53/EC (ELV):</b>	Yes
<b>EU Directive 2002/95/EC (RoHS):</b>	Yes
<b>EU RoHS Compliance Date (mm/dd/yyyy):</b>	04/01/2005
<b>EU Directive 2002/96/EC (WEEE):</b>	Yes
<b>EU Directive 2003/11/EC (BFR):</b>	Yes
<b>CA Prop 65 (CJ for Wire &amp; Cable):</b>	Yes
<b>MII Order #39 (China RoHS):</b>	Yes

#### Flame Test

<b>UL Flame Test:</b>	NFPA 262
<b>C(UL) Flame Test:</b>	FT6

#### Plenum/Non-Plenum

<b>Plenum (Y/N):</b>	Yes
----------------------	-----

### Electrical Characteristics (Overall)

**Nom. Characteristic Impedance:**

<b>Impedance (Ohm)</b>
50

**Nom. Inductance:**

<b>Inductance (µH/ft)</b>
.18

**Nom. Capacitance Conductor to Conductor:**

<b>Capacitance (pF/ft)</b>
27.5

**Nom. Capacitance Cond. to Other Conductor & Shield:**

<b>Capacitance (pF/ft)</b>
49.5

**Nominal Velocity of Propagation:**

<b>VP (%)</b>
---------------

## 6548PA Multi-Conductor - Pro Audio and Intercom Systems

69

**Nom. Conductor DC Resistance:**

**DCR @ 20°C (Ohm/1000 ft)**  
16.4

**Nominal Outer Shield DC Resistance:**

**DCR @ 20°C (Ohm/1000 ft)**  
15.3

**Max. Operating Voltage - UL:**

**Voltage**  
300 V RMS

**Max. Recommended Current:**

**Current**  
1.5 Amps per conductor @ 25°C

### Notes (Overall)

**Notes:** Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
6548PA 0081000	1,000 FT	125.000 LB	GRAY	C	12 FS PR #22 FEP SLF

**Notes:**  
C = CRATE REEL PUT-UP.

Revision Number: 1    Revision Date: 04-18-2008

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.