

8232A Coax - RG-59/U Type

For more Information
please call

1-800-Belden1

**Description:**

20 AWG solid .032" bare copper conductor, gas-injected foam HDPE insulation, bare copper braid shields (95% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	20	Solid	BC - Bare Copper	.032

Insulation**Insulation Material:**

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.145

Inner Shield**Inner Shield Material:**

Type	Inner Shield Material	Coverage (%)
Braid	BC - Bare Copper	95

Inner Jacket**Inner Jacket Material:**

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	.225

Outer Shield**Outer Shield Material:**

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	80

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.315 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +75°C

UL Temperature Rating: 60°C

Non-UL Temperature Rating: 75°C

Bulk Cable Weight: 63 lbs/1000 ft.

Max. Recommended Pulling Tension: 125 lbs.

Min. Bend Radius (Install)/Minor Axis: 3.250 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	59/U

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
----------------	-----------------------

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes - When supported by a messenger wire

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	88232

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)
75

Nom. Inductance:

Inductance (μH/ft)
0.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
16.2

Nominal Velocity of Propagation:

VP (%)
83

Nominal Delay:

Delay (ns/ft)
1.22

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
10.0

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
2.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
2.8

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)

1	.3
3.6	.6
10	.9
71.5	2.1
135	3.0
270	4.2
360	4.8
540	5.9
720	7.0
750	7.1
1000	8.3
1500	10.5
2250	13.4
3000	15.9

Max. Operating Voltage - UL:

Voltage
300 V RMS

Minimum Structural Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
5	850	21
851	3000	15

Sweep Test**Sweep Testing:**

100% sweep tested 5 MHz to 3 GHz.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8232A 0101000	1,000 FT	68.000 LB	BLACK	C	#20 GIFHDLPE BRD PVC BRD PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 04-06-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.