

8259 Coax - RG-58A/U Type

For more Information
please call

1-800-Belden1



Description:

RG-58A/U type, 20 AWG stranded (19x33) .035" tinned copper conductor, polyethylene insulation, tinned copper braid shield (95% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	20	19x33	TC - Tinned Copper	.035

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
PE - Polyethylene	.116

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.0275

Overall Cable

Overall Nominal Diameter: 0.193 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +75°C

Non-UL Temperature Rating: 75°C

Bulk Cable Weight: 24 lbs/1000 ft.

Max. Recommended Pulling Tension: 42 lbs.

Min. Bend Radius (Install)/Minor Axis: 2 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

RG Type: 58A/U

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Suitability - Aerial: Yes - when supported by a messenger wire

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

50

Nom. Inductance:

Inductance (µH/ft)

0.092

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

30.8

Nominal Velocity of Propagation:

VP (%)

66

Nominal Delay:

Delay (ns/ft)

1.54

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

10.8

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

4.1

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)

1	0.4
10	1.5
50	3.7
100	5.4
200	8.1
400	12.4
700	17.7
900	21.1
1000	22.8

Max. Operating Voltage - Non-UL:

Voltage

1400 V RMS

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8259 010U1000	1,000 FT	26.000 LB	BLACK		RG-58A/U 50 OHMS COAX
8259 010U500	500 FT	14.000 LB	BLACK		RG-58A/U 50 OHMS COAX

8259 010100	100 FT	3.300 LB	BLACK		RG-58A/U 50 OHMS COAX
8259 0101000	1,000 FT	27.000 LB	BLACK	C	RG-58A/U 50 OHMS COAX
8259 010500	500 FT	14.000 LB	BLACK	C	RG-58A/U 50 OHMS COAX

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.