Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



7806R Coax - RG-58 Type

For more Information please call

1-800-Belden1



Description:

RG-58 type, 19 AWG solid .037" bare copper conductor, gas-injected foam HDPE insulation, Duofoil® (100% coverage) + tinned copper braid shield (90% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	19	Solid	BC - Bare Copper	.037

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.110

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	90

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.195 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +75°C
UL Temperature Rating:	80°C
Bulk Cable Weight:	26 lbs/1000 ft.
Max. Recommended Pulling Tension:	40 lbs.
Min. Bend Radius (Install)/Minor Axis:	1.900 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes

Page 1 of 3 01-06-2012

Detailed Specifications & Technical Data





7806R Coax - RG-58 Type

EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	58/U
Series Type:	RF 195
Flame Test	
UL Flame Test:	UL1666 Vertical Shaft
CSA Flame Test:	FT4
Suitability	
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes - When supported by a messenger
Plenum/Non-Plenum	
Plenum (Y/N):	No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:



Nom. Inductance:



Nom. Capacitance Conductor to Shield:



Nominal Velocity of Propagation:



Nominal Delay:



Nom. Conductor DC Resistance:



Nominal Outer Shield DC Resistance:

```
DCR @ 20°C (Ohm/1000 ft)
4.2
```

Maximum VSWR:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Max. VSWR
		5	6000	1.25:1

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
30	2.0
50	2.5
150	4.0
220	4.9
450	7.1
900	10.3
1500	13.7
1800	15.2
2000	16.1

Page 2 of 3 01-06-2012

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



7806R Coax - RG-58 Type

2500	18.3	
3000	20.5	
4500	26.5	
5800	31.2	
6000	32.0	

Max. Power Rating:

Freq. (MHz)	Rating (W)
30	890
50	694
150	403
220	336
450	231
900	162
1500	124
1800	113
2000	107
2500	95
3000	87
3500	80
4500	70
5800	62
6000	61

Max. Operating Voltage - UL:

Voltage 300 V RMS

Notes (Overall)

Notes: 100% Sweep tested. 6 GHz. Belden® The Wire in Wireless®

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7806R 0101000	1,000 FT	28.000 LB	BLACK	С	RF195 WIRELESS 500HM COAXFRPVC
7806R 010500	500 FT	16.500 LB	BLACK	С	RF195 WIRELESS 50OHM COAXFRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 09-30-2009

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.