

7810R Coax - RG-8 Type

For more Information
please call

1-800-Belden1

**Description:**

RG-8 type, 10 AWG solid .108" bare copper-covered aluminum conductor, gas-injected foam HDPE insulation, Duobond® II + tinned copper braid shield (95% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	10	Solid	BCCA - Bare Copper Covered Aluminum	.108

Insulation**Insulation Material:**

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.285

Outer Shield**Outer Shield Material:**

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.403 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +75°C
UL Temperature Rating:	80°C
Bulk Cable Weight:	86.600 lbs/1000 ft.
Max. Recommended Pulling Tension:	150 lbs.
Min. Bend Radius (Install)/Minor Axis:	4 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

RG Type:	8/U
----------	-----

Series Type:	RF 400
--------------	--------

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
----------------	-----------------------

C(UL) Flame Test:	FT4
-------------------	-----

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Aerial:	Yes - When supported by a messenger
-----------------------	-------------------------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

50

Nom. Inductance:

Inductance (μH/ft)

0.060

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

23.0

Nominal Velocity of Propagation:

VP (%)

86

Nominal Delay:

Delay (ns/ft)

1.17

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

1.34

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2

Maximum VSWR:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Max. VSWR
		5	6000	1.25:1

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
30	0.7
50	0.9
150	1.5
220	1.8
450	2.7
900	3.8
1500	5.1
1800	5.6
2000	6.0
2500	6.7
3000	7.5

3500	8.2
4500	9.5
5800	11.1
6000	11.4

Max. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
30	0.70
50	0.93
150	1.58
220	1.94
450	2.83
900	4.06
1500	5.32
1800	5.98
2000	6.35
2500	7.08
3000	7.97
3500	8.80
4500	10.23
5800	12.00
6000	12.23

Max. Power Rating:

Freq. (MHz)	Rating (W)
30	3427
50	2588
150	1428
220	1195
450	817
900	575
1500	437
1800	399
2000	375
2500	334
3000	305
3500	282
4500	247
5800	217
6000	213

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Sweep Test

Sweep Testing: 100% Sweep tested to 6 GHz.

Misc. Information (Overall)**Notes (Overall)**

Notes: 100% Sweep tested. 6 GHz. Belden® The Wire in Wireless®

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7810R 0101000	1,000 FT	95.000 LB	BLACK	C	#10 LDPE/FHDPE SH FRPVC
7810R 010500	500 FT	47.000 LB	BLACK	C	#10 LDPE/FHDPE SH FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 09-30-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.