ENGLISH MEASUREMENT VERSION



7950A Composite - Composite Data, Audio, Video, Security and Control Cable



For more Information please call

1-800-Belden1



Description:

Siamese Composite - (1)Cat 5 4-pair, 24 AWG unshielded plus (4)16 AWG stranded (65x34) bare copper conductors, polyolefin insulation on the pairs; PVC insulation on the conductors, overall F-R PVC jacket. Jacket sequentially marked.

Twisted Pair

Physical Characteristics

Conductor

AWG:

| # Pairs | AWG | Stranding | Conductor Material | Dia. (in.) |
|---------|-----|-----------|--------------------|------------|
| 4 | 24 | Solid | BC - Bare Copper | 0.020 |

Insulation

Insulation Material:

| Insulation Material | Dia. (in.) |
|---------------------|------------|
| PO - Polyolefin | 0.036 |

Twisted Pair Color Code Chart:

| Number | Color |
|--------|--------------------------------|
| 1 | White/Blue Stripe and Blue |
| 2 | White/Orange Stripe and Orange |
| 3 | White/Green Stripe and Green |
| 4 | White/Brown Stripe and Brown |

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.) 0.195

Outer Jacket Ripcord:

Yes

Outer Jacket Color Code Chart:

Color Blue

Electrical Characteristics

Premise Cable Electricals:

| Freq. (MHz) | Max. Attenuation (dB/100 m) | Min. NEXT (dB) | Min. PSNEXT (dB) | Min. SRL (dB) | Fitted Imp. (Ohms) |
|-------------|-----------------------------|----------------|------------------|---------------|--------------------|
| 1.0 | 2.000 | 62 | N/A | 23 | 100 ± 15% |
| 4.0 | 4.100 | 53 | N/A | 23 | 100 ± 15% |
| 8.0 | 5.800 | 48 | N/A | 23 | 100 ± 15% |
| 10.0 | 6.500 | 47 | N/A | 23 | 100 ± 15% |
| 16.0 | 8.200 | 44 | N/A | 23 | 100 ± 15% |
| 20.0 | 9.300 | 42 | N/A | 23 | 100 ± 15% |
| 25.0 | 10.400 | 41 | N/A | 22 | 100 ± 15% |
| 31.25 | 11.700 | 39 | N/A | 21 | 100 ± 15% |
| 62.5 | 17.000 | 35 | N/A | 18 | 100 ± 15% |
| 100 | 22.000 | 32 | N/A | 16 | 100 ± 15% |

Page 1 of 4 01-06-2012

ENGLISH MEASUREMENT VERSION



7950A Composite - Composite Data, Audio, Video, Security and Control Cable

Multi Conductor

Physical Characteristics

Conductor

AWG:

| # Conductors | AWG | Stranding | Conductor Material | Dia. (in.) |
|--------------|-----|-----------|--------------------|------------|
| 4 | 16 | 65x34 | BC - Bare Copper | 0.059 |

Insulation

Insulation Material:

| Insulation Material | Dia. (in.) |
|--------------------------|------------|
| PVC - Polyvinyl Chloride | 0.079 |

Insulation Color Code Chart:

| Number | Color |
|--------|-------|
| 1 | Red |
| 2 | White |
| 3 | Green |
| 4 | Black |

Electrical Characteristics

Nom. Capacitance Conductor to Conductor:



Nominal Velocity of Propagation:



Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 9.380

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Current
5 Amps per conductor @ 25°C

Other Electrical Characteristic 1:

Third party verified to TIA/EIA-568-B.2, Category 5

Physical Characteristics (Overall)

Conductor

Outer Shield

Outer Shield Material:

Outer Shield Material Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 0.390 in.

Mechanical Characteristics (Overall)

| Operating Temperature Range: | -20°C To +75°C |
|------------------------------|---------------------|
| Bulk Cable Weight: | 95.000 lbs/1000 ft. |

Page 2 of 4 01-06-2012





7950A Composite - Composite Data, Audio, Video, Security and Control Cable

| Max. Recommended Pulling Tension: | 160.000 lbs. |
|--|--------------|
| Min. Bend Radius (Install)/Minor Axis: | 4.500 in. |

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

| NEC/(UL) Specification: | CMR |
|---------------------------------------|----------------------------------|
| CEC/C(UL) Specification: | CMG |
| Other Standards: | ISO/IEC 11801, Category 5 |
| EU CE Mark: | Yes |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (mm/dd/yyyy): | 04/01/2005 |
| EU Directive 2002/96/EC (WEEE): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |
| Telecommunications Standards: | ANSI/TIA/EIA-568.B.2, Category 5 |
| Other Specification: | NEMA WC-63.1, Category 5 |
| Flame Test | |
| UL Flame Test: | UL1666 Riser |

C(UL) Flame Test: FT4

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Max. Operating Voltage - UL:

Voltage 300 V RMS

Notes (Overall)

Notes: Overall jacket sequentially marked.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|--------------|--------|-------------|--------------|-------|---------------------|
| 7950A 337500 | 500 FT | 54.000 LB | GREEN, LIGHT | С | COMPOSITE CABLE PVC |

Notes:

C = CRATE REEL PUT-UP.

Revision Date: 02-11-2008 Revision Number: 0

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

Page 3 of 4

ENGLISH MEASUREMENT VERSION



7950A Composite - Composite Data, Audio, Video, Security and Control Cable

All sales of Belden products are subject to Belden's standard terms and conditions of sale.
Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Page 4 of 4 01-06-2012