

8138 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/485



For more Information
please call

1-800-Belden1



Description:

28 AWG stranded (7x36) TC conductors, Datalene® insulation, overall Beldfoil® (100% coverage) + TC braid shield (65% coverage), 28 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
8	28	7x36	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material
Datalene®	FPE - Foam Polyethylene

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100
2		Braid	TC - Tinned Copper	65

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
28	7x36		TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.330 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue & Blue/White
2	White/Orange & Orange/White
3	White/Green & Green/White
4	White/Brown & Brown/White
5	White/Gray & Gray/White
6	Red/Blue & Blue/Red
7	Red/Orange & Orange/Red
8	Red/Green & Green/Red

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)
0.880	13.600

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +80°C

8138 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/485

UL Temperature Rating:	80°C (UL AWM Style 2919)
------------------------	--------------------------

Bulk Cable Weight:	58 lbs/1000 ft.
--------------------	-----------------

Min. Bend Radius (Install)/Minor Axis:	3.300 in.
--	-----------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CL2
-------------------------	-----

AWM Specification:	UL Style 2919 (30 V 80°C)
--------------------	---------------------------

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

120

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

11

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

20

Nominal Velocity of Propagation:

VP (%)

78

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

65

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

3.7

Max. Operating Voltage - UL:

Voltage

30 V RMS (UL AWM Style 2919); 150 V RMS

Max. Recommended Current:

Current

0.7 Amps per conductor @ 25°C

Notes (Overall)

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

8138 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/485

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8138 060100	100 FT	5.600 LB	CHROME		8 PR #28 FHDPE SH PVC
8138 0601000	1,000 FT	51.000 LB	CHROME	C	8 PR #28 FHDPE SH PVC
8138 060500	500 FT	27.000 LB	CHROME	C	8 PR #28 FHDPE SH PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-15-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.