

8760 Multi-Conductor - Shielded Twisted Pair Cable



For more Information
please call

1-800-Belden1

**Description:**

18 AWG stranded (16x30) tinned copper conductors, polyethylene insulation, twisted pair, overall Beldfoil® shield (100% coverage), 20 AWG stranded tinned copper drain wire, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
1	18	16x30	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (in.)
PE - Polyethylene	.019

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
20	7x28		TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.028

Overall Cable

Overall Nominal Diameter: 0.222 in.

Pair**Pair Color Code Chart:**

Number	Color
1	Black & Clear

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)
2.500	4.800

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
UL Temperature Rating:	60°C (UL AWM Style 2092)
Bulk Cable Weight:	23 lbs/1000 ft.
Max. Recommended Pulling Tension:	62 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.250 in.

8760 Multi-Conductor - Shielded Twisted Pair Cable

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2092 (300 V 60°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	88760, 87760 or 82760

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
57

Nom. Inductance:

Inductance (μH/ft)
.18

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
29.8

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
44

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
6.5

Max. Operating Voltage - UL:

Voltage
300 V RMS (UL AWM Style 2092)

Max. Recommended Current:

Current
5.2 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8760 060U1000	1,000 FT	27.000 LB	CHROME		2 #18 LDPE SH PVC

8760 Multi-Conductor - Shielded Twisted Pair Cable

8760 060U500	500 FT	14.000 LB	CHROME		2 #18 LDPE SH PVC
8760 0601000	1,000 FT	25.000 LB	CHROME		2 #18 LDPE SH PVC
8760 06010000	10,000 FT	270.000 LB	CHROME	C Y	2 #18 LDPE SH PVC
8760 0602000	2,000 FT	54.000 LB	CHROME	C	2 #18 LDPE SH PVC
8760 060250	250 FT	7.000 LB	CHROME		2 #18 LDPE SH PVC
8760 060500	500 FT	14.000 LB	CHROME	C	2 #18 LDPE SH PVC
8760 0605000	5,000 FT	145.000 LB	CHROME	C	2 #18 LDPE SH PVC
8760 0609999	1,000 FT	28.000 LB	CHROME		2 #18 LDPE SH PVC

Notes:

C = CRATE REEL PUT-UP.

Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN.MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

Revision Number: 2 Revision Date: 08-17-2011

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.