

ENGLISH MEASUREMENT VERSION

82512 Multi-Conductor - Computer Cable for EIA RS-232 Applications



For more Information please call

1-800-Belden1



Description:

24 AWG stranded (7x32) tinned copper conductors, plenum, FEP insulation, twisted pair, overall Beldfoil shield (100% coverage), 24 AWG stranded TC drain wire, Flamarrest® jacket.

Physical Characteristic	ics (Overall)						
Conductor							
AWG:							
	WG Stranding Conductor Material						
1 12 24	7x32 TC - Tinned Copper						
Insulation							
Insulation Material:							
Insulation Material	Wall Thickness (in.)						
FEP - Fluorinated Ethylene	FEP - Fluorinated Ethylene Propylene 1.006						
Outen Objelel							
Outer Shield Outer Shield Material:							
Beldfoil®	Type Outer Shield Material Coverage (%) Tape Aluminum Foil-Polyester Tape 100						
	Belatolike Lape Aluminum Foil-Polyester Lape 100						
Outer Shield Drain Wire							
AWG Stranding Drain W							
24 7x32 TC - Tini	ned Copper						
Outer Jacket							
Outer Jacket Outer Jacket Material:							
	e Outer Jacket Material Nom. Wall Thickness (in.)						
Outer Jacket Material:	e Outer Jacket Material Nom. Wall Thickness (in.) LS PVC - Low Smoke Polyvinyl Chloride .015						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest®							
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable	LS PVC - Low Smoke Polyvinyl Chloride .015						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride .015						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable	LS PVC - Low Smoke Polyvinyl Chloride .015						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable Overall Nominal Diame	LS PVC - Low Smoke Polyvinyl Chloride .015						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable Overall Nominal Diame Pair	LS PVC - Low Smoke Polyvinyl Chloride 0.015						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable Overall Nominal Diame Pair Pair Color Code Chart: Number Color	LS PVC - Low Smoke Polyvinyl Chloride 0.015						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable Overall Nominal Diame Pair Pair Color Code Chart: Number Color 1 Black	LS PVC - Low Smoke Polyvinyl Chloride 0.015 eter: 0.278 in.						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable Overall Nominal Diame Pair Pair Color Code Chart: Number Color 1 Black 2 Black	LS PVC - Low Smoke Polyvinyl Chloride 0.015 eter: 0.278 in. & Red						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable Overall Nominal Diame Pair Pair Color Code Chart: Number Color 1 Black 2 Black 3 Black 4 Black	LS PVC - Low Smoke Polyvinyl Chloride 0.015 eter: 0.278 in. & Red & White & Green & Blue						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable Overall Nominal Diame Pair Pair Color Code Chart: Number Color 1 Black 2 Black 3 Black 4 Black 5 Black	LS PVC - Low Smoke Polyvinyl Chloride .015 eter: 0.278 in. & Red & White & Green & Blue & Yellow						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable Overall Nominal Diame Pair Pair Color Code Chart: Number Color 1 Black 2 Black 3 Black 4 Black 5 Black 6 Black	LS PVC - Low Smoke Polyvinyl Chloride 0.015 eter: 0.278 in. & Red & Red & White & Green & Blue & Blue & Yellow & Brown						
Outer Jacket Material: Outer Jacket Trade Name Flamarrest® Overall Cable Overall Nominal Diame Pair Pair Color Code Chart: Number Color 1 Black 2 Black 3 Black 4 Black 5 Black 6 Black 7 Black	LS PVC - Low Smoke Polyvinyl Chloride .015 eter: 0.278 in. & Red & White & Green & Blue & Yellow						

 9
 Red & Green

 10
 Red & Blue

 11
 Red & Yellow

 12
 Red & Brown

 Single Conductor+
 Yellow

Pair Lay Length & Direction:

Lay Length	(in.)
2.500	

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

82512 Multi-Conductor - Computer Cable for EIA RS-232 Applications

lechanical Characteristics (Overall)			
Operating Temperature Range:	0°C To +60°C		
Bulk Cable Weight:	56.100 lbs/1000 ft.		
Max. Recommended Pulling Tension:	143 lbs.		
Min. Bend Radius (Install)/Minor Axis:	3 in.		
pplicable Specifications and Agency Co	ompliance (Overall)		
Applicable Standards & Environmental Progr			
NEC/(UL) Specification:	СМР		
CEC/C(UL) Specification:	СМР		
EU CE Mark:	Yes		
EU Directive 2000/53/EC (ELV):	Yes		
EU Directive 2002/95/EC (RoHS):	Yes		
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005		
EU Directive 2002/96/EC (WEEE):	Yes		
EU Directive 2003/11/EC (BFR):	Yes		
CA Prop 65 (CJ for Wire & Cable):	Yes		
MII Order #39 (China RoHS):	Yes		
Flame Test			
UL Flame Test:	NFPA 262		
C(UL) Flame Test:	FT6		
Plenum/Non-Plenum			
Plenum (Y/N):	Yes		
lectrical Characteristics (Overall)			
Nom. Inductance:			
Inductance (µH/ft) .17			
Nom. Capacitance Conductor to Conductor: Capacitance (pF/ft)			
23			
Nom. Capacitance Cond. to Other Conductor & Sh	ield:		
Capacitance (pF/ft)			
42			
Nom. Conductor DC Resistance: DCR @ 20°C (Ohm/1000 ft)			
15			
Max. Operating Voltage - UL:			
Voltage 300 V RMS			
Max. Recommended Current:			
Current 1.5 Amps per conductor @ 25°C			

Related Documents:

No related documents are available for this product

Put Ups and Colors:



ENGLISH MEASUREMENT VERSION

82512 Multi-Conductor - Computer Cable for EIA RS-232 Applications

Item #	Putup	Ship Weight	Color	Notes	Item Desc
82512 8771000	1,000 FT	60.000 LB	NATURAL	С	12H PR #24 FEP FS FLMRST

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-16-2008

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.