

88105 Multi-Conductor - Low Cap. Computer Cable for EIA RS-232/422/485 Applications



For more Information
please call

1-800-Belden1

**Description:**

24 AWG stranded (7x32) tinned copper conductors, plenum, foam FEP insulation, twisted pairs, overall Beldfoil shield (100% coverage), 24 AWG stranded TC drain wire, fluorocopolymer jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
5	24	7x32	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material
FFEP - Foam Fluorinated Ethylene Propylene

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
24	7x32	TC - Tinned Copper	

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVDF - Fluorocopolymer

Overall Cable

Overall Nominal Diameter: 0.267 in.

Pair**Pair Color Code Chart:**

Number	Color
1	White/Blue & Blue/White
2	White/Orange & Orange/White
3	White/Green & Green/White
4	White/Brown & Brown/White
5	White/Gray & Gray/White

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +150°C
Bulk Cable Weight:	43.300 lbs/1000 ft.
Max. Recommended Pulling Tension:	60 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.700 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

88105 Multi-Conductor - Low Cap. Computer Cable for EIA RS-232/422/485 Applications

NEC/(UL) Specification:	CMP
-------------------------	-----

CEC/C(UL) Specification:	CMP
--------------------------	-----

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	NFPA 262
----------------	----------

C(UL) Flame Test:	FT6
-------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

100

Nom. Inductance:

Inductance (μH/ft)

0.21

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

12.95

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

23.3

Nominal Velocity of Propagation:

VP (%)

78

Nominal Delay:

Delay (ns/ft)

1.3

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

24

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

14

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

1.54 Amps per conductor @ 25°C

Related Documents:

88105 Multi-Conductor - Low Cap. Computer Cable for EIA RS-232/422/485 Applications

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
88105 0081000	1,000 FT	44.000 LB	GRAY	C	5#24 PR FS SOLEF
88105 008500	500 FT	23.500 LB	GRAY	C	5#24 PR FS SOLEF

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.