Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

٠

•

89272 Twinax - 78 Ohm Twinax

<u> 2120-222</u>

For more Information please call

1-800-Belden1



Description:

78 ohm, 20 AWG stranded (7x28) .038" tinned copper conductors, plenum, FEP Teflon® insulation, tinned copper braid shield (93% coverage), FEP Teflon® jacket.

Physical Characteristics (Overall)	
Physical Characteristics (Overall) Conductor	
AWG:	
Pairs AWG Stranding Conductor Material Dia. (in.)
1 20 7x28 TC - Tinned Copper .038	
Insulation	
Insulation Material:	
Insulation Trade Name Insulation Material Teflon® FEP - Fluorinated Ethylene F	Propylene 0.074
· · · · ·	
Outer Shield Outer Shield Material:	
Type Outer Shield Material Coverage (%)	
Braid TC - Tinned Copper 93	
Outer Jacket	
Outer Jacket Material:	
Outer Jacket Trade Name Outer Jacket Material	
Teflon® FEP - Fluorinated Ethylen	ie Propylene
Overall Cable	
Overall Nominal Diameter:	0.198 in.
Pair	
Pair Color Code Chart: Number Color	
1 Clear & Blue	
Mechanical Characteristics (Overall)	
Operating Temperature Range:	-70°C To +200°C
Bulk Cable Weight:	32 lbs/1000 ft.
Max. Recommended Pulling Tension:	68 lbs.
Min. Bend Radius (Install)/Minor Axis:	2 in.
Annlinghle Credifications and Agency C	
Applicable Specifications and Agency C Applicable Standards & Environmental Prog	
NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



89272 Twinax - 78 Ohm Twinax

EU Directive 2002/96/EC (WEEE):	Yes			
EU Directive 2003/11/EC (BFR):	Yes			
CA Prop 65 (CJ for Wire & Cable):	Yes			
MII Order #39 (China RoHS):	Yes			
Flame Test				
UL Flame Test:	NFPA 262			
C(UL) Flame Test:	FT6			
Suitability				
Suitability - Indoor:	Yes			
Suitability - Outdoor:	Yes			
Suitability - Aerial:	Yes			
Suitability - Burial:	Yes			
Plenum/Non-Plenum				
Plenum (Y/N):	Yes			
Non-Plenum Number:	9272			

Electrical Characteristics (Overall)

Nom. Characteristic Impedance: Impedance (Ohm) 78

Nom. Inductance:

Inductance (µH/ft)

0.200

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

18.4

Nominal Velocity of Propagation:

VP (%) 69.5

Nominal Delay:

Delay (ns/ft) 1.46

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

9.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

3.9

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)

1	0.6	
10	2.1	
50	5.0	
100	7.5	
200	11.0	
400	16.0	

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Operating Voltage - Non-UL:

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



Voltage

600 V RMS

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc. Suitable for aerial applications when supported by a messenger wire.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
89272 0061000	1,000 FT	38.000 LB	BLUE, LIGHT	С	2#20 FEP BRD FEP 78 OHM
89272 006500	500 FT	17.000 LB	BLUE, LIGHT	С	2#20 FEP BRD FEP 78 OHM

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.