# **Detailed Specifications & Technical Data**





## 9252 Coax - 50 Ohm Coax

For more Information please call

1-800-Belden1



## **Description:**

22 AWG stranded (27x36) .030" tinned copper conductor, polyethylene insulation, tinned copper braid shield (95% coverage), non-contaminating PVC jacket.

Physical Characteristics (Overall)	
Conductor AWG:	
# Coax   AWG   Stranding   Conductor   Material   Dia. (in.     1   22   27x36   TC - Tinned Copper   .030	
Insulation Insulation Material: Insulation Material Dia. (in.)	
PE - Polyethylene .096	
Outer Shield Outer Shield Material:	
TypeOuter Shield MaterialCoverage (%)BraidTC - Tinned Copper95	
Outer Jacket Outer Jacket Material:	
Outer Jacket Material	
PVCNC - Polyvinyl Chloride Non-Contaminating	
Overall Cable Overall Nominal Diameter:	0.160 in.
Mechanical Characteristics (Overall)	
Operating Temperature Range:	-40°C To +80°C
UL Temperature Rating:	80°C
Bulk Cable Weight:	17 lbs/1000 ft.
Bulk Cable Weight: Max. Recommended Pulling Tension:	17 lbs/1000 ft. 38 lbs.
Max. Recommended Pulling Tension: Min. Bend Radius (Install)/Minor Axis:	38 lbs. 1.600 in.
Max. Recommended Pulling Tension:	38 lbs. 1.600 in. mpliance (Overall)
Max. Recommended Pulling Tension: Min. Bend Radius (Install)/Minor Axis: Applicable Specifications and Agency Co	38 lbs. 1.600 in. mpliance (Overall)
Max. Recommended Pulling Tension: Min. Bend Radius (Install)/Minor Axis: Applicable Specifications and Agency Con Applicable Standards & Environmental Progra	38 lbs. 1.600 in. mpliance (Overall) ams
Max. Recommended Pulling Tension: Min. Bend Radius (Install)/Minor Axis: Applicable Specifications and Agency Con Applicable Standards & Environmental Progra NEC/(UL) Specification:	38 lbs. 1.600 in. mpliance (Overall) ams CMX
Max. Recommended Pulling Tension: Min. Bend Radius (Install)/Minor Axis: Applicable Specifications and Agency Con Applicable Standards & Environmental Progra NEC/(UL) Specification: CEC/C(UL) Specification:	38 lbs. 1.600 in. mpliance (Overall) ams CMX CMX
Max. Recommended Pulling Tension: Min. Bend Radius (Install)/Minor Axis: Applicable Specifications and Agency Con Applicable Standards & Environmental Progra NEC/(UL) Specification: CEC/C(UL) Specification: AWM Specification:	38 lbs.   1.600 in.   mpliance (Overall)   ams   CMX   CMX   UL Style 1354 (30 V 80°C)
Max. Recommended Pulling Tension: Min. Bend Radius (Install)/Minor Axis: Applicable Specifications and Agency Con Applicable Standards & Environmental Progra NEC/(UL) Specification: CEC/C(UL) Specification: AWM Specification: EU CE Mark:	38 lbs.   1.600 in.   mpliance (Overall)   ams   CMX   CMX   UL Style 1354 (30 V 80°C)   Yes
Max. Recommended Pulling Tension: Min. Bend Radius (Install)/Minor Axis: Applicable Specifications and Agency Con Applicable Standards & Environmental Progra NEC/(UL) Specification: CEC/C(UL) Specification: AWM Specification: EU CE Mark: EU Directive 2000/53/EC (ELV):	38 lbs.   1.600 in.   mpliance (Overall)   ams   CMX   CMX   UL Style 1354 (30 V 80°C)   Yes   Yes

# **Detailed Specifications & Technical Data**

## ENGLISH MEASUREMENT VERSION



### 9252 Coax - 50 Ohm Coax

EU Directive 2003/11/EC (BFR):	Yes		
CA Prop 65 (CJ for Wire & Cable):	Yes		
MII Order #39 (China RoHS):	Yes		
Military Specification:	MIL-DTL-17H; M17/54-00001		
RG Type:	122/U		
lenum/Non-Plenum			
Plenum (Y/N):	No		

#### **Electrical Characteristics (Overall)**

Nom. Characteristic Impedance:

Impedance (Ohm) 50

Nom. Inductance:

Inductance (µH/ft)

0.077

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

30.8

Nominal Velocity of Propagation:

**VP (%)** 66

Nominal Delay:

Delay (ns/ft) 1.54

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

17.1

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

5.2

## Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	0.4
10	1.7
50	4.5
100	7.0
200	11.0
400	16.5
700	23.5
900	27.3
1000	29.0

#### Max. Operating Voltage - UL:

Voltage 300 V RMS (CMX)

30 V RMS (UL AWM Style 1354)

### Max. Operating Voltage - Non-UL:

Voltage 1100 V RMS

Max. Operating Voltage - Other:

VoltageDescriptionMilitary Specification1400 V RMS



#### **Related Documents:**

No related documents are available for this product

#### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9252 0101000	1,000 FT	20.000 LB	BLACK		M17/157-00001 COAX

**Revision Number: 2** Revision Date: 03-17-2009

#### © 2012 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warrate or guidance. Begulatory information is for guidance on purposes only. Breduct users are responsible for to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.