



For more Information
please call

1-800-Belden1



Description:

13 conductor (1 coax, 12 cond), remote control and video cable, foam polyethylene (coax) and PVC (cond) insulation, coax: BC braid (95% coverage), overall TC braid (80% coverage), overall PVC jacket.

Coax

Physical Characteristics

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	22	7x30	TC - Tinned Copper	.031

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
FPE - Foam Polyethylene	.146

Inner Shield

Inner Shield Material:

Type	Inner Shield Material	% Coverage (%)
Braid	BC - Bare Copper	95

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	.208

Electrical Characteristics

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
17.3

Nominal Velocity of Propagation:

VP (%)
78

Nominal Delay:

Delay (ns/ft)
1.3

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
14.4

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
2.55

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
.5	.2

1	.29
5	.67
10	.95
100	3.1
200	4.4
400	6.3

Max. Operating Voltage - UL: 300 V RMS

Multi Conductor

Physical Characteristics

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
12	20	7x28	TC - Tinned Copper	0.038

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
PVC - Polyvinyl Chloride	.070

Electrical Characteristics

Max. Operating Voltage - UL:

Voltage	Voltage
300 V RMS	300 V RMS

Physical Characteristics (Overall)

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	80

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.406 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 156.000 lbs/1000 ft.

Max. Recommended Pulling Tension: 305.000 lbs.

Min. Bend Radius (Install)/Minor Axis: 5.000 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL2X

AWM Specification: UL Style 1007 (singles), UL Style 1354 (Coax), UL Style 2594 (Overall)

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

9262 Composite - Cables for TV Cameras and CCTV

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Max. Operating Voltage - UL:

Voltage
300 V RMS

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9262 008100	100 FT	15.000 LB	GRAY		12#20,1#22,PVC,FPE S PVC
9262 0081000	1,000 FT	157.000 LB	GRAY	C	12#20,1#22,PVC,FPE S PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 0 Revision Date: 09-16-2011

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.