


9406 Multi-Conductor - Audio, Control and Instrumentation Cable

For more Information
please call

1-800-Belden1



Description:

22 AWG stranded (7x30) TC conductors, semi-rigid PVC insulation, twisted pairs, individually shielded w/Beldfoil® (100% coverage), 22 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
2	22	7x30	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material
S-R PVC - Semi-Rigid Polyvinyl Chloride

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: 7x30

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.173 x 0.280 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & White
2	Black & Yellow

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)
1.250	9.600

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

9406 Multi-Conductor - Audio, Control and Instrumentation Cable

UL Temperature Rating:	80°C (UL AWM Style 2464)
Bulk Cable Weight:	31 lbs/1000 ft.
Max. Recommended Pulling Tension:	36 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.800 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

C(UL) Flame Test:	FT4
--------------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
----------------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

50

Nom. Inductance:

Inductance (µH/ft)

0.095

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

50

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

95

Nominal Velocity of Propagation:

VP (%)

60

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

15

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 13 Ohm/1000 ft

Max. Operating Voltage - UL:

Voltage

300 V RMS (UL AWM Style 2464)

Max. Recommended Current:

9406 Multi-Conductor - Audio, Control and Instrumentation Cable

Current

2.3 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9406 T35U1000	1,000 FT	32.000 LB	BEIGE, PALE FAWN		2 #22 FS PR PVC PVC
9406 T35U500	500 FT	16.500 LB	BEIGE, PALE FAWN		2 #22 FS PR PVC PVC
9406 T35100	100 FT	3.800 LB	BEIGE, PALE FAWN		2 #22 FS PR PVC PVC
9406 T351000	1,000 FT	33.000 LB	BEIGE, PALE FAWN	C	2 #22 FS PR PVC PVC
9406 T35500	500 FT	17.000 LB	BEIGE, PALE FAWN		2 #22 FS PR PVC PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 11-10-2009

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.