

## 9544 Multi-Conductor - Computer Cable for EIA RS-232 Applications



For more Information  
please call

1-800-Belden1



### Description:

24 AWG stranded (7x32) tinned copper conductors, conductors cabled, semi-rigid PVC insulation, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Conductors	AWG	Stranding	Conductor Material
30	24	7x32	TC - Tinned Copper

#### Insulation

##### Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.010

#### Outer Shield

##### Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

##### Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
24	7x32	TC - Tinned Copper	

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.040

#### Overall Cable

##### Overall Cabling Lay Length & Direction:

Length (in.)
4.92

##### Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green
5	Orange
6	Blue
7	White/Black
8	Red/Black
9	Green/Black
10	Orange/Black
11	Blue/Black
12	Black/White
13	Red/White
14	Green/White
15	Blue/White
16	Black/Red

## 9544 Multi-Conductor - Computer Cable for EIA RS-232 Applications

17	White/Red
18	Orange/Red
19	Blue/Red
20	Red/Green
21	Orange/Green
22	Black/White/Red
23	White/Black/Red
24	Red/Black/White
25	Green/Black/White
26	Orange/Black/White
27	Blue/Black/White
28	Black/Red/Green
29	White/Red/Green
30	Red/Black/Green

**Overall Nominal Diameter:** 0.380 in.

### Mechanical Characteristics (Overall)

<b>Operating Temperature Range:</b>	-30°C To +80°C
<b>UL Temperature Rating:</b>	80°C (UL AWM Style 2464)
<b>Bulk Cable Weight:</b>	99.100 lbs/1000 ft.
<b>Max. Recommended Pulling Tension:</b>	165 lbs.
<b>Min. Bend Radius (Install)/Minor Axis:</b>	4 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

<b>NEC/(UL) Specification:</b>	CMG
<b>CEC/C(UL) Specification:</b>	CMG
<b>AWM Specification:</b>	UL Style 2464 (300 V 80°C)
<b>EU CE Mark:</b>	Yes
<b>EU Directive 2000/53/EC (ELV):</b>	Yes
<b>EU Directive 2002/95/EC (RoHS):</b>	Yes
<b>EU RoHS Compliance Date (mm/dd/yyyy):</b>	04/01/2005
<b>EU Directive 2002/96/EC (WEEE):</b>	Yes
<b>EU Directive 2003/11/EC (BFR):</b>	Yes
<b>CA Prop 65 (CJ for Wire &amp; Cable):</b>	Yes
<b>MII Order #39 (China RoHS):</b>	Yes

#### Flame Test

**C(UL) Flame Test:** FT4

#### Plenum/Non-Plenum

**Plenum (Y/N):** No

### Electrical Characteristics (Overall)

#### Nom. Capacitance Conductor to Conductor:

**Capacitance (pF/ft)**  
30

#### Nom. Capacitance Cond. to Other Conductor & Shield:

**Capacitance (pF/ft)**  
55

#### Nom. Conductor DC Resistance:

**DCR @ 20°C (Ohm/1000 ft)**

## 9544 Multi-Conductor - Computer Cable for EIA RS-232 Applications

25

### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

18

### Max. Operating Voltage - UL:

Voltage

300 V RMS (UL AWM Style 2464)

### Max. Recommended Current:

Current

1.75 Amps per conductor @ 25°C

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9544 060100	100 FT	10.300 LB	CHROME		30 #24 PVC FS PVC
9544 0601000	1,000 FT	102.000 LB	CHROME	C	30 #24 PVC FS PVC
9544 060500	500 FT	51.500 LB	CHROME	C	30 #24 PVC FS PVC

#### Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1    Revision Date: 05-14-2007

© 2012 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.