

9566 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1

**Description:**

24 AWG solid tinned copper conductors, PVC insulation, twisted pairs, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
6	24	Solid	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.010

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.032

Overall Cable

Overall Nominal Diameter: 0.289 in.

Pair**Pair Color Code Chart:**

Number	Color
1	White & Blue
2	White & Orange
3	White & Green
4	White & Brown
5	White & Gray
6	Red & Blue

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
Non-UL Temperature Rating:	80°C
Bulk Cable Weight:	37.200 lbs/1000 ft.
Max. Recommended Pulling Tension:	61 lbs.
Min. Bend Radius (Install)/Minor Axis:	3 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG

9566 Multi-Conductor - Audio, Control and Instrumentation Cable

AWM Specification:	UL Style 2576 (150 V 80°C)
---------------------------	----------------------------

EU CE Mark:	Yes
--------------------	-----

EU Directive 2000/53/EC (ELV):	Yes
---------------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
--	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
--	------------

EU Directive 2002/96/EC (WEEE):	Yes
--	-----

EU Directive 2003/11/EC (BFR):	Yes
---------------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
--	-----

MII Order #39 (China RoHS):	Yes
------------------------------------	-----

Flame Test

UL Flame Test:	UL1685 FT4 Loading
-----------------------	--------------------

C(UL) Flame Test:	FT4
--------------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
----------------------	----

Electrical Characteristics (Overall)**Nom. Capacitance Conductor to Conductor:**

Capacitance (pF/ft)

22

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

24.4

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

1.4 Amps per conductor @ 20°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9566 060U1000	1,000 FT	42.000 LB	CHROME		6 PR #24 PVC FRPVC
9566 060U500	500 FT	21.500 LB	CHROME		6 PR #24 PVC FRPVC
9566 0601000	1,000 FT	45.000 LB	CHROME	C	6 PR #24 PVC FRPVC
9566 060500	500 FT	23.500 LB	CHROME	C	6 PR #24 PVC FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

9566 Multi-Conductor - Audio, Control and Instrumentation Cable

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.