

89728 Multi-Conductor - Multi-Pair Snake Cable

 For more Information
 please call

1-800-Belden1

**Description:**

24 AWG stranded (7x32) TC conductor, plenum, foam FEP insulation, twisted pairs, individually shielded w/Beldfoil (100% coverage) each with 24 AWG stranded TC drain wire, overall fluorocopolymer jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
4	24	7x32	TC - Tinned Copper	.024

Insulation**Insulation Material:**

Insulation Material	Dia. (in.)
FFEP - Foam Fluorinated Ethylene Propylene	.062

Inner Shield**Inner Shield Material:**

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper
Inner Shield Color Code Chart:

Number	AWG	Color
1	24	Red
2	24	Green
3	24	Blue
4	24	Blue

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVDF - Fluorocopolymer

Overall Cable
Overall Nominal Diameter: 0.307 in.
Pair**Pair Color Code Chart:**

Number	Color
1	White/Blue & Blue/White
2	White/Orange & Orange/White
3	White/Green & Green/White
4	White/Brown & Brown/White

Mechanical Characteristics (Overall)
Operating Temperature Range: -20°C To +150°C

89728 Multi-Conductor - Multi-Pair Snake Cable

Bulk Cable Weight:	55.500 lbs/1000 ft.
Max. Recommended Pulling Tension:	50 lbs.
Min. Bend Radius (Install)/Minor Axis:	3.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
C(UL) Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	9728

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

100

Nom. Inductance:

Inductance (μH/ft)

0.24

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

13.5

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

22.5

Nominal Velocity of Propagation:

VP (%)

76

Nominal Delay:

Delay (ns/ft)

1.3

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

24

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 14.400 Ohm/1000 ft

Nom. Attenuation:

89728 Multi-Conductor - Multi-Pair Snake Cable

Freq. (MHz)	Attenuation (dB/100 ft.)
.384	0.74
.7056	0.87
.768	0.89
1.024	0.95
1.4112	1.03
1.536	1.06
2.048	1.17
2.8224	1.37
3.072	1.44
4.096	1.67
5.6448	1.89
6.144	1.96
8.192	2.26
11.2896	2.59
12.288	2.71
24.576	3.73

Max. Operating Voltage - UL:**Voltage**

300 V RMS

Max. Recommended Current:**Current**

2.0 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
89728 0081000	1,000 FT	50.000 LB	GRAY	C	4 SH PR #24 FFEP SLF
89728 008500	500 FT	26.500 LB	GRAY	C	4 SH PR #24 FFEP SLF

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 11-10-2010

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.