

89842 Multi-Conductor - Low Capacitance Computer and Computer P.O.S. Cable



For more Information
please call

1-800-Belden1

**Description:**

24 AWG stranded (7x32) tinned copper conductors, twisted pairs, foam FEP insulation, overall 100% Beldfoil® shield, 24 AWG stranded tinned copper drain wire, overall tinned copper braid shield (90% coverage), FEP jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
2	24	7x32	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Trade Name	Insulation Material
Teflon®	FFEP - Foam Fluorinated Ethylene Propylene

Outer Shield**Outer Shield Material:**

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	90

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
24	7x32		TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Trade Name	Outer Jacket Material
Teflon®	FEP - Fluorinated Ethylene Propylene

Overall Cable

Overall Nominal Diameter: 0.305 in.

Pair**Pair Color Code Chart:**

Number	Color
1	White/Blue & Blue/White
2	White/Orange & Orange/White

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)
2.000	6.000

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +150°C

Bulk Cable Weight: 44 lbs/1000 ft.

Max. Recommended Pulling Tension: 68 lbs.

Min. Bend Radius (Install)/Minor Axis: 3.100 in.

89842 Multi-Conductor - Low Capacitance Computer and Computer P.O.S. Cable

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
C(UL) Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	9842

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
120

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
12

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
22

Nominal Velocity of Propagation:

VP (%)
76

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
24

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
3.1

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
4 Amps per conductor @ 25°C

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Related Documents:

89842 Multi-Conductor - Low Capacitance Computer and Computer P.O.S. Cable

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
89842 0021000	1,000 FT	49.000 LB	RED	C	2 PR #24 FFEPR SH FEP
89842 002500	500 FT	25.500 LB	RED	C	2 PR #24 FFEPR SH FEP

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-17-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.