

89880 Coax - Coaxial Cable - Thicknet 10Base5 Ethernet

For more Information
please call

1-800-Belden1

**Description:**

12 AWG solid .086" bare copper conductor, foam FEP insulation, Duobond IV® quad shield (100% coverage), fluorocopolymer jacket.

Usage (Overall)

Suitable Applications: Thick Ethernet

Physical Characteristics (Overall)**Conductor**

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	12	Solid	BC - Bare Copper	.086

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
FFEP - Foam Fluorinated Ethylene Propylene	.245

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	90
3	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
4		Braid	TC - Tinned Copper	90

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVDF - Fluorocopolymer

Overall Cable

Overall Nominal Diameter: 0.375 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-25°C To +150°C
UL Temperature Rating:	150°C
Bulk Cable Weight:	137 lbs/1000 ft.
Max. Recommended Pulling Tension:	255 lbs.
Min. Bend Radius (Install)/Minor Axis:	6 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMP, CL2P
CEC/C(UL) Specification:	CMP
IEEE Specification:	IEEE802.3 10Base5

89880 Coax - Coaxial Cable - Thicknet 10Base5 Ethernet

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Customer Part Number Reference Specification:	DEC Part No. 17-00324-00
---	--------------------------

Flame Test

UL Flame Test:	NFPA 262
----------------	----------

CSA Flame Test:	FT6
-----------------	-----

Suitability

Suitability - Outdoor:	Yes
------------------------	-----

Suitability - Burial:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Non-Plenum Number:	9880
--------------------	------

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)	Tolerance (Ohms)
50	+/- 2

Nom. Inductance:

Inductance (μH/ft)
.0645

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
26.0

Nominal Velocity of Propagation:

VP (%)
78

Nominal Delay:

Delay (ns/ft)
1.30

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
1.42

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
1.52

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.18
5	.37 max
10	.52 max
50	1.15
100	1.65
200	2.45
400	3.8

89880 Coax - Coaxial Cable - Thicknet 10Base5 Ethernet

700	5.6
900	6.8
1000	7.2

Max. Power Rating:

Freq. (MHz)	Rating (W)
1	15900
5	6928
10	4802
50	1992
100	1344
200	900
400	602
700	438
900	382
1000	361

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Notes (Overall)

Notes: Ring-band stripes every 2.5 meters to aid users in tap placement.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
89880 0031000	1,000 FT	134.000 LB	ORANGE	C	#11H FFEP SH SOL COAX
89880 0031640	1,640 FT	224.680 LB	ORANGE	C Z	#11H FFEP SH SOL COAX

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 2 Revision Date: 09-23-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.