


89892 Multi-Conductor - 10 Base 5 Transceiver



For more Information
please call

1-800-Belden1

**Description:**

20 AWG stranded (7x28) tinned copper conductors, FEP insulation, twisted pairs, individual Beldfoil® shields (100% coverage), overall polyester isolation tape and Duofoil® shield plus a tinned copper braid shield (95% coverage), fluorocopolymer jacket.

Usage (Overall)

Suitable Applications: 10Base5 Transceiver

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	20	7x28	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material
Teflon®	FEP - Fluorinated Ethylene Propylene

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: 7x30

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVDF - Fluorocopolymer

Overall Cable

Overall Cabling Separator Material: Polyester Tape

Overall Nominal Diameter: 0.359 in.

Pair

Pair Color Code Chart:

Number	Color
1	Gray & White
2	Yellow & Orange
3	Blue & Green

4	Red & Black
---	-------------

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +150°C
UL Temperature Rating:	150°C
Bulk Cable Weight:	116 lbs/1000 ft.
Max. Recommended Pulling Tension:	175 lbs.
Min. Bend Radius (Install)/Minor Axis:	3.600 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
IEEE Specification:	IEEE802.3
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Customer Part Number Reference Specification:	1700321-02

Flame Test

UL Flame Test:	NFPA 262
C(UL) Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	9901

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)	Tolerance (Ohms)
78	± 5

Nom. Inductance:

Inductance (µH/ft)
.2

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
16.7

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
29.5

Nominal Velocity of Propagation:

VP (%)
78

Nominal Delay:

Delay (ns/ft)
1.30

89892 Multi-Conductor - 10 Base 5 Transceiver

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
9.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
1.5

Max. Attenuation:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Attenuation (dB/100 m)
	10			6

Max. Operating Voltage - UL:

Voltage
150 V RMS

Max. Recommended Current:

Current
2.8 Amps per conductor @ 25°C

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
89892 0011000	1,000 FT	101.000 LB	BROWN	C	4 FS PR#20 FEP SH SLF
89892 001500	500 FT	50.000 LB	BROWN	C	4 FS PR#20 FEP SH SLF

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 09-23-2008

© 2012 Belden, Inc
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.