

9737 Multi-Conductor - Multi-Pair Snake Cable

For more Information
please call

1-800-Belden1

**Description:**

24 AWG stranded (7x32) TC conductors, Datalene® insulation, twisted pairs, individually shielded w/Beldfoil® (100% coverage), 24 AWG stranded TC drain wire, overall PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

| # Pairs | AWG | Stranding | Conductor Material | Dia. (in.) |
|---------|-----|-----------|--------------------|------------|
| 19 | 24 | 7x32 | TC - Tinned Copper | .024 |

Insulation**Insulation Material:**

| Insulation Trade Name | Insulation Material | Dia. (in.) |
|-----------------------|-------------------------|------------|
| Datalene® | FPE - Foam Polyethylene | .061 |

Inner Shield**Inner Shield Material:**

| Inner Shield Trade Name | Type | Inner Shield Material | Coverage (%) |
|-------------------------|------|------------------------------|--------------|
| Beldfoil® (Z-Fold®) | Tape | Aluminum Foil-Polyester Tape | 100 |

Inner Shield Drain Wire AWG:

| AWG |
|-----|
| 24 |

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

| Outer Jacket Material |
|--------------------------|
| PVC - Polyvinyl Chloride |

Overall Cable

Overall Nominal Diameter: 0.671 in.

Pair**Pair Color Code Chart:**

| Number | Color |
|--------|----------------|
| 1 | Black & Red |
| 2 | Black & White |
| 3 | Black & Green |
| 4 | Black & Blue |
| 5 | Black & Yellow |
| 6 | Black & Brown |
| 7 | Black & Orange |
| 8 | Red & White |
| 9 | Red & Green |
| 10 | Red & Blue |
| 11 | Red & Yellow |
| 12 | Red & Brown |
| 13 | Red & Orange |
| 14 | Green & White |

| | |
|----|----------------|
| 15 | Green & Blue |
| 16 | Green & Yellow |
| 17 | Green & Brown |
| 18 | Green & Orange |
| 19 | White & Blue |

Pair Lay Length & Direction:

| Lay Length (in.) | Twists/ft. (twist/ft) |
|------------------|-----------------------|
| 1.750 | 6.850 |

Mechanical Characteristics (Overall)

| | |
|---|--------------------------|
| Operating Temperature Range: | -20°C To +80°C |
| UL Temperature Rating: | 60°C (UL AWM Style 2493) |
| Bulk Cable Weight: | 200 lbs/1000 ft. |
| Max. Recommended Pulling Tension: | 325 lbs. |
| Min. Bend Radius (Install)/Minor Axis: | 6.750 in. |

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

| | |
|--|----------------------------|
| NEC/(UL) Specification: | CM |
| CEC/C(UL) Specification: | CM |
| AWM Specification: | UL Style 2493 (300 V 60°C) |
| EU CE Mark: | Yes |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (mm/dd/yyyy): | 01/01/2004 |
| EU Directive 2002/96/EC (WEEE): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MIL Order #39 (China RoHS): | Yes |

Flame Test

| | |
|-----------------------|-------------------|
| UL Flame Test: | UL1685 UL Loading |
|-----------------------|-------------------|

Plenum/Non-Plenum

| | |
|----------------------|----|
| Plenum (Y/N): | No |
|----------------------|----|

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

| Impedance (Ohm) |
|-----------------|
| 100 |

Nom. Inductance:

| Inductance (µH/ft) |
|--------------------|
| 0.23 |

Nom. Capacitance Conductor to Conductor:

| Capacitance (pF/ft) |
|---------------------|
| 12.5 |

Nom. Capacitance Cond. to Other Conductor & Shield:

| Capacitance (pF/ft) |
|---------------------|
| 23.2 |

Nominal Velocity of Propagation:

| VP (%) |
|--------|
|--------|

9737 Multi-Conductor - Multi-Pair Snake Cable

76

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

24

 Ind. Pair Nominal Shield DC Resistance @ 20
 Deg. C: 15 Ohm/1000 ft

Nom. Attenuation:

| Freq. (MHz) | Attenuation (dB/100 ft.) |
|-------------|--------------------------|
| .384 | 0.74 |
| .7056 | 0.87 |
| .768 | 0.88 |
| 1.024 | 0.94 |
| 1.4112 | 1.01 |
| 1.536 | 1.03 |
| 2.048 | 1.13 |
| 2.8224 | 1.29 |
| 3.072 | 1.35 |
| 4.096 | 1.57 |
| 5.6448 | 1.78 |
| 6.144 | 1.84 |
| 8.192 | 2.13 |
| 11.2896 | 2.45 |
| 12.288 | 2.57 |
| 24.576 | 3.57 |

Max. Operating Voltage - UL:

Voltage

300 V RMS (UL AWM Style 2493)

Max. Recommended Current:

Current

1.9 Amps per conductor @ 25°C

Notes (Overall)

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|--------------|----------|-------------|--------|-------|------------------------|
| 9737 0601000 | 1,000 FT | 231.000 LB | CHROME | C | 19 FS PR #24 FHDPE PVC |

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-17-2008

© 2012 Belden, Inc.
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and

9737 Multi-Conductor - Multi-Pair Snake Cable

the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.