

9209 Coax - Miniature

For more Information
please call

1-800-Belden1



Description:

23 AWG solid .022" bare copper conductor, polyethylene insulation, Duofoil® + tinned copper braid shield (95% coverage), polyethylene jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	23	Solid	BC - Bare Copper	.022

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
PE - Polyethylene	.146

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PE - Polyethylene

Overall Cable

Overall Nominal Diameter: 0.220 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -55°C To +80°C

Non-UL Temperature Rating: 80°C

Bulk Cable Weight: 27 lbs/1000 ft.

Max. Recommended Pulling Tension: 43 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes

MII Order #39 (China RoHS): Yes

RG Type: 59/U

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Suitability - Aerial: Yes - When supported by a messenger wire

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (µH/ft)
.118

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
21.0

Nominal Velocity of Propagation:

VP (%)
66

Nominal Delay:

Delay (ns/ft)
1.56

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
20.4

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
4.5

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.4
3.58	.5
5	.84
7	.98
10.0	1.17
67.5	2.85
71.5	2.90
100	3.35
135	3.95
143	4.05
180	4.55
270	5.60
360	6.55
540	8.30
720	9.65
750	9.90
1000	11.60

Max. Operating Voltage - Non-UL:

Voltage
2300 V RMS

Other Electrical Characteristic 1: Impedance tested in accordance w/ASTM D-4566 para 43.2 opt 2 using a 75 Ohm fixed bridge&termination.

Other Electrical Characteristic 2: Return loss tested in accordance w/ASTM D-4566 para 45.3 using a 75 Ohm fixed bridge&termination.

Minimum Structural Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
5.000	216.000	27.000
216.000	850.000	23.000

Sweep Test

Sweep Testing: 100% Sweep tested 5 MHz to 850 MHz.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9209 010U1000	1,000 FT	29.000 LB	BLACK		75 OHM MINI VIDEO CABLE
9209 010U500	500 FT	15.000 LB	BLACK		75 OHM MINI VIDEO CABLE

Revision Number: 2 Revision Date: 09-30-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.