

## 9232 Coax - RG-11/U Type

For more Information  
please call

1-800-Belden1

**Description:**

15 AWG stranded (19x27) .064" bare copper conductor, foam HDPE insulation, paper tape separator, bare copper braid shields (90% coverage), CSPE - Chlorosulphonated Polyethylene jacket.

**Physical Characteristics (Overall)****Conductor****AWG:**

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	15	19x27	BC - Bare Copper	.064

**Insulation****Insulation Material:**

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.312

**Inner Shield****Inner Shield Material:**

Type	Inner Shield Material	Coverage (%)
Braid	BC - Bare Copper	90

**Inner Jacket****Inner Jacket Material:**

Inner Jacket Material	Nom. Dia. (in.)
PE - Polyethylene	.391

**Outer Shield****Outer Shield Material:**

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	82

**Outer Shield Separator Material:** Paper Tape

**Outer Jacket****Outer Jacket Material:**

Outer Jacket Material
CSPE - Chlorosulphonated Polyethylene

**Overall Cable**

**Overall Nominal Diameter:** 0.520 in.

**Mechanical Characteristics (Overall)**

**Operating Temperature Range:** -20°C To +75°C

**UL Temperature Rating:** 60°C

**Non-UL Temperature Rating:** 75°C

**Bulk Cable Weight:** 135 lbs/1000 ft.

**Max. Recommended Pulling Tension:** 239 lbs.

**Min. Bend Radius (Install)/Minor Axis:** 5.500 in.

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

AWM Specification:	UL Style 1641 (30 V 60°C)
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	11/U

### Flame Test

UL Flame Test:	UL1685 UL Loading, VW-1
----------------	-------------------------

### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Electrical Characteristics (Overall)

### Nom. Characteristic Impedance:

Impedance (Ohm)
75

### Nom. Inductance:

Inductance (μH/ft)
0.097

### Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
17.3

### Nominal Velocity of Propagation:

VP (%)
78

### Nominal Delay:

Delay (ns/ft)
1.30

### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
3.1

### Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
1.6

### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
1.6

### Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)
--------------------------------------

# Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

9232 Coax - RG-11/U Type

1.000	0.100
3.600	0.300
10.000	0.500
71.500	1.200
135.000	1.800
270.000	2.600
360.000	3.100
540.000	3.900
720.000	4.700
750.000	4.800
1000.000	5.700

## Max. Operating Voltage - UL:

Voltage
30 V RMS

## Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

**Other Electrical Characteristic 1:** Nominal Capacitance 1st Shield to 2nd Shield: 205 pF/ft.

**Other Electrical Characteristic 2:** Nominal Voltage Breakdown: 20K V RMS

## Minimum Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
		5	450	21

## Sweep Test

**Sweep Testing:** 100% sweep tested 5 MHz to 450 MHz.

## Misc. Information (Overall)

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9232 0101000	1,000 FT	142.000 LB	BLACK	C	75 OHM TRIAX
9232 010500	500 FT	76.500 LB	BLACK	C	75 OHM TRIAX

#### Notes:

C = CRATE REEL PUT-UP.

Revision Number: 9    Revision Date: 01-07-2011

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.