

For more Information
please call

1-800-Belden1



Description:

100 ohm, 20 AWG stranded (7x28) .037" one tinned/ one bare copper conductors, polyethylene insulation, Duofoil® + TC braid shield (95% coverage), high-density polyethylene jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	20	7x28	TC - Tinned Copper
			BC - Bare Copper

Insulation

Insulation Material:

Insulation Material
PE - Polyethylene

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PE - Polyethylene	.236

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Shield Flooding Grease: Polyethylene Grease

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
HDPE - High Density Polyethylene

Overall Cable

Overall Nominal Diameter: 0.330 in.

Pair

Pair Color Code Chart:

Number	Color
1	Natural & Natural

Mechanical Characteristics (Overall)

Operating Temperature Range: -55°C To +80°C

Bulk Cable Weight: 60.500 lbs/1000 ft.

Max. Recommended Pulling Tension: 115 lbs.

Min. Bend Radius (Install)/Minor Axis: 3.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Suitability

Suitability - Burial: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

100

Nom. Inductance:

Inductance (μH/ft)

0.155

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

14.5

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

23.0

Nominal Velocity of Propagation:

VP (%)

66

Nominal Delay:

Delay (ns/ft)

1.54

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

9.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)

1	0.4
10	1.1
50	2.5
100	4.1
200	6.4
400	10.2

Max. Operating Voltage - Non-UL:

Voltage

600 V RMS

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9815 0101000	1,000 FT	69.000 LB	BLACK	C	TW PR #20 PE PE BRD PE
9815 010500	500 FT	34.500 LB	BLACK		TW PR #20 PE PE BRD PE

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.