# **Detailed Specifications & Technical Data**

## **ENGLISH MEASUREMENT VERSION**



# 9874 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information please call

1-800-Belden1



# **Description:**

20 AWG stranded (7x28) TC conductors, polypropylene insulation, twisted pairs, individually shielded w/Beldfoil® (100% coverage), 22 AWG stranded TC drain wire, overall PVC jacket.

# **Physical Characteristics (Overall)**

#### Conductor

#### AWG:

# Pairs	AWG	Stranding	<b>Conductor Material</b>
6	20	7x28	TC - Tinned Copper

#### Insulation

#### **Insulation Material:**

# Insulation Material PP - Polypropylene

#### **Inner Shield**

#### Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

#### Inner Shield Drain Wire AWG:



Inner Shield Drain Wire Stranding: 19x34

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

# **Outer Jacket**

#### **Outer Jacket Material:**

# Outer Jacket Material PVC - Polyvinyl Chloride

### **Overall Cable**

Overall Nominal Diameter: 0.445 in.

#### **Pair**

# Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown

## Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)
1.750	6.850

# **Mechanical Characteristics (Overall)**

Operating Temperature Range: -20°C To +80°C

Page 1 of 3 01-06-2012

# **Detailed Specifications & Technical Data**





# 9874 Multi-Conductor - Audio, Control and Instrumentation Cable

UL Temperature Rating:	80°C (UL AWM Style 2919)	
Bulk Cable Weight:	102 lbs/1000 ft.	
Max. Recommended Pulling Tension:	256 lbs.	
Min. Bend Radius (Install)/Minor Axis:	4.700 in.	

# **Applicable Specifications and Agency Compliance (Overall)**

# **Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2919 (30 V 80°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### **Flame Test**

UL Flame Test: UL1685 UL Loading

### Plenum/Non-Plenum

Plenum (Y/N): No

# **Electrical Characteristics (Overall)**

Nom. Characteristic Impedance:

Impedance	(Ohm)
50	

Nom. Inductance:



Nom. Capacitance Conductor to Conductor:



Nom. Capacitance Cond. to Other Conductor & Shield:



Nominal Velocity of Propagation:



Nom. Conductor DC Resistance:

DCR @ 20°C	(Ohm/1000	ft)
10.5		

Ind. Pair Nominal Shield DC Resistance @ 20 11.300 Ohm/1000 ft Deg. C:

Max. Operating Voltage - UL:

Voltage 30 V RMS (UL AWM Style 2919) 300 V RMS (CM)

Max. Recommended Current:

Page 2 of 3 01-06-2012

# **Detailed Specifications & Technical Data**

#### **ENGLISH MEASUREMENT VERSION**



## 9874 Multi-Conductor - Audio, Control and Instrumentation Cable

Current
2.7 Amps per conductor @ 25°C

#### **Related Documents:**

No related documents are available for this product

### **Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9874 060100	100 FT	11.700 LB	CHROME	С	6 FS PR #20 PP PVC
9874 0601000	1,000 FT	109.000 LB	CHROME	С	6 FS PR #20 PP PVC
9874 060500	500 FT	56.000 LB	CHROME	С	6 FS PR #20 PP PVC

#### Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-18-2008

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Page 3 of 3 01-06-2012