


9409 Multi-Conductor - 300V Power-Limited Tray Cable



For more Information
please call

1-800-Belden1

**Description:**

18 AWG pairs stranded (19x30) tinned copper conductors, twisted pairs, PVC insulation, unshielded, PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	18	19x30	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material
PVC - Polyvinyl Chloride

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.037

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Direction
Left-hand Lay

Overall Nominal Diameter: 0.230 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

Bulk Cable Weight: 27 lbs/1000 ft.

Max. Recommended Pulling Tension: 49 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.250 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: PLTC, ITC, CMG

CEC/C(UL) Specification: CMG

9409 Multi-Conductor - 300V Power-Limited Tray Cable

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	UL1685 FT4 Loading
----------------	--------------------

C(UL) Flame Test:	FT4
-------------------	-----

IEEE Flame Test:	1202
------------------	------

ICEA Flame Test:	T-29-520
------------------	----------

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	Yes
------------------------	-----

Sunlight Resistance:	Yes
----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)**Electrical Characteristics (Overall)****Nom. Capacitance Conductor to Conductor:**

Capacitance (pF/ft)

26

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

5.96

Max. Operating Voltage - UL:

Voltage

300 V RMS (PLTC

CMG)

150 V RMS (ITC)

Max. Recommended Current:

Current

9 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9409 060U1000	1,000 FT	28.000 LB	CHROME		2 #18 PVC PVC
9409 060U500	500 FT	15.000 LB	CHROME		2 #18 PVC PVC
9409 0602500	2,500 FT	70.000 LB	CHROME		2 #18 PVC PVC

9409 Multi-Conductor - 300V Power-Limited Tray Cable

Revision Number: 1 Revision Date: 11-23-2011

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.