


9493 Triad - 300V Power-Limited Tray Cable



For more Information
please call

1-800-Belden1

**Description:**

18 AWG triads stranded (19x30) tinned copper conductors, twisted triads, PVC insulation, unshielded, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Triads	AWG	Stranding	Conductor Material
1	18	19x30	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material
PVC - Polyvinyl Chloride

Insulation Resistance:

2500 MegaOhms @ 500 Volts DC/1000 ft.

Inner Shield**Inner Shield Color Code Chart:**

Number	Color
1	Black & White & Red

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.037

Outer Jacket Ripcord:

Yes

Overall Cable**Overall Nominal Diameter:**

0.242 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

Bulk Cable Weight: 35.900 lbs/1000 ft.

Max. Recommended Pulling Tension: 62 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.250 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: PLTC, ITC, CMG

CEC/C(UL) Specification: CMG

AWM Specification: UL Style 2464 (300 V 80°C)

EU CE Mark: Yes

9493 Triad - 300V Power-Limited Tray Cable

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Flame Test

CSA Flame Test:	FT4
IEEE Flame Test:	1202
ICEA Flame Test:	T-29-520

Suitability

Suitability - Burial:	Yes
Sunlight Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft)
.15

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
31.8

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
5.96

Max. Operating Voltage - UL:

Voltage	Description
20,000 V RMS	Breakdown between conductors (Short Term)

Max. Recommended Current:

Current
9 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9493 060U1000	1,000 FT	38.000 LB	CHROME		3 #18 PVC PVC
9493 060U500	500 FT	20.000 LB	CHROME		3 #18 PVC PVC
9493 0602500	2,500 FT	97.500 LB	CHROME		3 #18 PVC PVC

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not

9493 Triad - 300V Power-Limited Tray Cable

ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.