

9L28050 Flat - Gray Ribbon 9L280XX Series



For more Information
please call

1-800-Belden1

**Description:**

Belden's .050" pitch gray ribbon cable was designed for general purpose electronic interconnect applications. The cable provides reliable mass-termination to standard IDC connectors.

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
50	28	7x36	TC - Tinned Copper

Conductor Spacing Center to Center: .050 +/- .002

Conductor Spacing Outside Center to Outside Center: 2.45 +/- .012

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.010

Insulation Resistance: >10, 000 Megaohms

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Overall Cable

Overall Nominal Thickness: .035 +/- .003

Overall Nominal Width: 2.50 +/- .012

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +105°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

UL AWM Style:	2651
UL Rating:	105°C, 300 V RMS, VW-1
CSA Specification:	AWM I A 105°C 300 V FT1
CSA Rating:	105°C, 300 V RMS, FT1
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	VW-1
----------------	------

CSA Flame Test:	FT1
-----------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)**Electrical Characteristics (Overall)****Nom. Characteristic Impedance:**

Description	Impedance (Ohm)
(GS)	150
(GSG)	105

Nom. Inductance:

Description	Inductance (µH/ft)
@ 1 MHz (GS)	.29
@ 1 MHz (GSG)	.20

Nom. Capacitance Conductor to Conductor:

Description	Capacitance (pF/ft)
@ 1 kHz (GSG)	18
@ 1 MHz (GS)	10
@ 1 MHz (GSG)	15

Nominal Velocity of Propagation:

Description	VP (%)
	72

Nominal Delay:

Delay (ns/ft)
1.40 NS/FT. (GSG)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
68.2 OHMS/1000 FT. MAX.

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
10	2.8
20	4.8
30	6.5
40	8.3
50	9.8
60	12
70	13
80	14
90	15.8
100	17

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
1 Amp per conductor @ 20°C

Dielectric Withstand Voltage:	2, 000 V RMS
-------------------------------	--------------

Typical Unbalanced Crosstalk:

9L28050 Flat - Gray Ribbon 9L280XX Series

Description	Pulse Rise Time (NS) (MHz)	Near End % (MHz)	Far End % (MHz)
10 ft. sample length	3	4.8	7
10 ft. sample length	5	3.5	4.7
10 ft. sample length	7	3	3

Notes (Overall)

Notes: GS=Ground-Signal Mode; GSG=Ground-Signal-Ground Mode

Polarity Identification (Overall)

Polarity Identification: RED POLARITY STRIPE ON #1 CONDUCTOR

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9L28050 008H100	100 FT	6.500 LB	GRAY		50 #28 STR PVC RIBBON

Revision Number: 1 Revision Date: 05-14-2007

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.