
Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



9L30050 Flat - Gray Ribbon 9L300XX Series



For more Information please call

1-800-Belden1



Description:

Belden's miniaturized .025" pitch gray ribbon cable provides higher signal density and greater design flexibility. The cable is manufactured to precise tolerances which allows for mass-termination to standard IDC connectors.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
50	30	7x38	TC - Tinned Copper

Conductor Spacing Center to Center: .025 +/- .002

Conductor Spacing Outside Center to Outside 1.225 +/- .009

Center:

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.0075

Insulation Resistance: > 10, 000 Megaohms

Outer Shield

Outer Shield Material:

Outer Shield Material Unshielded

Overall Cable

Overall Nominal Thickness: .027 +/- .002

Overall Nominal Width: 1.25 +/- .011

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +105°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL AWM Style:	2678
UL Rating:	105°C, 150 V, VW-1
CSA Specification:	AWM I A 105°C 150 V FT1
CSA Rating:	105°C, 150 V, FT1
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2005
EU Directive 2002/96/EC (WEEE):	Yes

Page 1 of 3 01-06-2012

Detailed Specifications & Technical Data





9L30050 Flat - Gray Ribbon 9L300XX Series

EU Directive 2003/11/EC (BFR):	Yes	
CA Prop 65 (CJ for Wire & Cable):	Yes	
MII Order #39 (China RoHS):	Yes	
Flame Test		
UL Flame Test:	VW-1	
CSA Flame Test:	FT1	
Plenum/Non-Plenum		
Plenum (Y/N):	No	

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Description	Impedance (Ohm)
(GS)	105
(GSG)	70

Nom. Inductance:

Description	Inductance (µH/ft)		
@ 1 MHz (GS)	.21		
@ 1 MHz (GSG)	.14		

Nom. Capacitance Conductor to Conductor:

Description	Capacitance (pF/ft)		
@ 1 kHz (GS)	18		
@ 1 kHz (GSG)	32		
@ 1 MHz (GS)	14		
@ 1 MHz (GSG)	24		

Nominal Velocity of Propagation:

Description	VP (%)
	66

Nominal Delay:

Delay (ns/ft) 1.52 NS/FT. (GSG)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 108 OHMS/1000 FT. MAX.

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
10	5.4
20	9.5
30	14.1
40	18
50	20.1
60	24.9
70	26.5
80	30
90	30.6
100	33

Max. Operating Voltage - UL:

Voltage 150 V RMS

Max. Recommended Current:

Current
0.5 Amps per conductor @ 20°C

Page 2 of 3 01-06-2012

Detailed Specifications & Technical Data





9L30050 Flat - Gray Ribbon 9L300XX Series

Dielectric Withstand Voltage: 2.000 V RMS

Typical Unbalanced Crosstalk:

Description	Pulse Rise Time (NS) (MHz)	Near End % (MHz)	Far End % (MHz)
10 ft. sample length	3	6	7.1
10 ft. sample length	5	5.4	7
10 ft. sample length	7	5	6.6

Notes (Overall)

Notes: GSG=Ground-Signal-Ground Mode

Polarity Identification (Overall)

Polarity Identification: RED POLARITY STRIPE ON #1 CONDUCTOR

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9L30050 008H100	100 FT	3.400 LB	GRAY		50 #30 STR PVC RIBBON

Revision Number: 1 Revision Date: 09-23-2008

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.