

## AX101034 Modular Connectors - USOC Modular Jack - MDVO style



For more Information  
please call

1-800-Belden1

**Description:**

USOC Modular Jack, RJ45, MDVO style, Almond

**Usage (Overall)**

**Suitable Applications:** Voice Applications

**Related Parts:** Compatible with Interface and MDVO Style Faceplates, Adapters, Boxes and Patch Panels

**Physical Characteristics (Connectivity)****Dimensions**

**Dimensions:**

Height (in.)	Width (in.)	Depth (in.)
0.850	0.770	1.350

**Materials**

**Materials:**

Description	Type	Material
Front Connection	Lead Frame	Copper Allow with 50u inch Gold over Nickel
Rear Connection	IDC	Copper Allow with Nickel Plating
Connector Body		Plastic - UL940V-0

**Color**

**Color:** Almond

**Wiring Scheme**

**Wiring Scheme:** USOC

**Weight**

**Weight:** 0.014 lbs.

**Included Parts**

**Included Parts:** 1 Clear Protective Cap

**Packaging**

**Packaging:** Individually packaged in a plastic bag. Standard pack of 50 units.

**Mechanical Characteristics (Connectivity)**

**Footprint/Type:** MDVO-Style

**Plug / Jack Compatibility:** RJ45, RJ11

**Termination Interface:**

Termination	Connection	Durabilities
Front	Mated Connection	1,000 cycles
Rear	Gas Tight IDC Connection	10 terminations

**Connector/Hardware Retention:** 20 lbs.

**Plug/Connector Retention:** 11.250 lbs.

**Storage Temperature Range:** -40°C To +70°C

**Installation Temperature Range:** -10°C To +60°C

**AX101034 Modular Connectors - USOC Modular Jack - MDVO style**

**Operating Temperature Range:** -10°C To +60°C

**Tool Compatibility:** Belden 110 Connecting Tool, MediaFlex Termination Station

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

**Other Standards:** FCC Part 68, Subpart F, IEC 60603-7

**EU Directive 2002/95/EC (RoHS):** Yes

**EU RoHS Compliance Date (mm/dd/yyyy):** 07/01/2006

**MII Order #39 (China RoHS):** EUP 50

**Safety Listing:** ACA, Bi-national (UL/CSA) Standard Listed

**Suitability**

**Suitability - Indoor:** Yes - Indoor

**Transmission Characteristics (Connectivity)**

**Dielectric Strength:** 1,000 V RMS @ 60 Hz for 1 minute

**Current Rating:** 1.500 A

**Insulation Resistance:** 500 M-Ohm Minimum

**Max. Contact Resistance:** 20 m-Ohm

**Termination Resistance:** 2.5 m-Ohm

**Notes (Overall)**

**Notes:** Please see Installation Guide PX101565

**Product Family****Part Number List:**

Item Number	Color
AX101033	Gray
AX101034	Almond
AX101035	White
AX101036	Black
AX101037	Orange (TIA 606)
AX101038	Red (TIA 606)
AX101039	Yellow (TIA 606)
AX101040	Green (TIA 606)
AX101041	Blue (TIA 606)
AX101042	Purple (TIA 606)
AX101043	Brown (TIA 606)
AX102565	Ivory

**Related Documents:**

No related documents are available for this product

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX101034	1 EA	0.024 LB			FLEX MODULE, USOC, ALMOND

Revision Number: 0    Revision Date: 12-17-2008

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or

## **AX101034 Modular Connectors - USOC Modular Jack - MDVO style**

exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.