

AX101871 Panels - MediaFlex Plate, Double gang



For more Information
please call

1-800-Belden1

**Description:**

MediaFlex Plate, Double gang

Usage (Overall)

Suitable Applications: -Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400, 1200, Fiber and Coax.

Related Parts: Compatible with MediaFlex inserts

Physical Characteristics (Connectivity)**Dimensions**

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
4.500	5.180	0.770

Materials

Materials:

Description	Material
Plate	Plastic - UL94V-0

Color

Color: Elec. White

Weight

Weight: 0.100 lbs.

Included Parts

Included Parts: windows, paper, 6-32 screws, installation guide

Packaging

Packaging: Individually packaged in a suitable plastic bag

Mechanical Characteristics (Connectivity)

Storage Temperature Range: -40°C To +70°C

Installation Temperature Range: -10°C To +60°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2006

MII Order #39 (China RoHS): EUP 50

Safety Listing: ACA, Bi-national (UL/CSA) Standard Listed

Suitability

Suitability - Indoor: Yes

Notes (Overall)

AX101871 Panels - MediaFlex Plate, Double gang

Notes: For proper installation refer to Installation Guide PX102063 included with the product or visit our web site at <http://www.belden.com>

Product Family**Part Numbers:**

description	Gray	Almond	Elec. White	Black
MediaFlex Plate Single Gang	AX101745	AX101746	AX101747	AX101748
MediaFlex Plate Double Gang	AX101869	AX101870	AX101871	AX101872

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX101871	1 EA	0.172 LB			MEDIAFLEX FACEPLATE DG ELEC WH

Revision Number: 0 Revision Date: 05-29-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.