

9819 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/422



For more Information
please call

1-800-Belden1

**Description:**

28 AWG stranded (7x36) TC conductors, polypropylene insulation, overall Beldfoil® (100% coverage) + TC braid shield (90% coverage), 28 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
18	28	7x36	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material
PP - Polypropylene

Outer Shield**Outer Shield Material:**

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	90

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
28	7x36	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.365 in.

Pair**Pair Color Code Chart:**

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown
7	Black & Orange
8	Red & White
9	Red & Green
10	Red & Blue
11	Red & Yellow
12	Red & Brown
13	Red & Orange
14	Green & White
15	Green & Blue
16	Green & Yellow

9819 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/422

17	Green & Brown
18	Green & Orange

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)
0.600	20.000

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
UL Temperature Rating:	60°C (UL AWM Style 2960)
Bulk Cable Weight:	75 lbs/1000 ft.
Max. Recommended Pulling Tension:	145 lbs.
Min. Bend Radius (Install)/Minor Axis:	3.700 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CL2
AWM Specification:	UL Style 2960 (30 V 60°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
100

Nom. Inductance:

Inductance (µH/ft)
.19

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
15.5

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
27.5

Nominal Velocity of Propagation:

VP (%)
66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
64.9

9819 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/422

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2

Max. Operating Voltage - UL:

Voltage

30 V RMS (UL AWM Style 2960); 150 V RMS

Max. Recommended Current:

Current

.65 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9819 060100	100 FT	8.300 LB	CHROME		18 PR #28 PP SH PVC
9819 0601000	1,000 FT	82.000 LB	CHROME	C	18 PR #28 PP SH PVC
9819 060500	500 FT	40.500 LB	CHROME	C	18 PR #28 PP SH PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-17-2008

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.