




AX100177 Modular Connectors - USOC EZ-MDVO Modular Jack - MDVO style



For more Information
please call

1-800-Belden1

**Description:**

USOC EZ-MDVO Modular Jack, RJ11, Yellow (TIA 606)

Usage (Overall)

Suitable Applications:

Voice Applications

Related Parts:

Compatible with Interface and MDVO Style Faceplates, Adapters, Boxes and Patch Panels

Physical Characteristics (Connectivity)**Dimensions**

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
0.710	0.750	1.250

Materials

Materials:

Description	Type	Material
Front Connection	Lead Frame	Copper Allow with 50u inch Gold over Nickel
Rear Connection	IDC	Copper Allow with Nickel Plating
Connector body		Plastic - UL940V-0

Color

Color:

Yellow (TIA 606)

Wiring Scheme

Wiring Scheme:

USOC

Weight

Weight:

0.013 lbs.

Included Parts

Included Parts:

Center Stuffercap Coded USOC

Packaging

Packaging:

Individually packaged in a plastic bag. Standard pack of 50 units.

Mechanical Characteristics (Connectivity)

Footprint/Type:

MDVO-Style

Plug / Jack Compatibility:

RJ11

Termination Interface:

Termination	Connection	Durabilities
Front	Mated Connection	1,000 cycles
Rear	Gas Tight IDC Connection	10 terminations

Connector/Hardware Retention:

20 lbs.

Plug/Connector Retention:

11.250 lbs.

Storage Temperature Range:

-40°C To +70°C

Installation Temperature Range:

-10°C To +60°C

AX100177 Modular Connectors - USOC EZ-MDVO Modular Jack - MDVO style

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

Other Standards:	FCC Part 68, Subpart F, IEC 60603-7
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2006
MII Order #39 (China RoHS):	EUP 50
Safety Listing:	ACA, Bi-national (UL/CSA) Standard Listed

Suitability

Suitability - Indoor:	Yes - Indoor
-----------------------	--------------

Transmission Characteristics (Connectivity)

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max. Contact Resistance:	20 m-Ohm
Termination Resistance:	2.5 m-Ohm

Notes (Overall)

Notes: Please See Installation Guide PX102753

Product Family**Part Number List:**

Item Number	Color
AX100171	Gray
AX100172	Almond
AX100173	White
AX100174	Black
AX100175	Orange (TIA 606)
AX100176	Red (TIA 606)
AX100177	Yellow (TIA 606)
AX100178	Green (TIA 606)
AX100179	Blue (TIA 606)
AX100180	Purple (TIA 606)
AX100181	Brown (TIA 606)

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX100177	1 EA	0.024 LB			EZ-MDVO UTP MODULE,

Revision Number: 0 Revision Date: 12-03-2008

 © 2012 Belden, Inc.
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

AX100177 Modular Connectors - USOC EZ-MDVO Modular Jack - MDVO style

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.