

B9C231 Fiber - Industrial Armored Cable - Riser

For more Information
please call

1-800-Belden1

**Description:**

FiberExpress Interlock Armor Optical Fiber cables have a rugged construction that affords superior protection in adverse environments yet can also be installed in general purpose, riser and plenum environments.

Physical Characteristics (Overall)

Fiber Type:	50/125/900 Micron
Number of Fibers:	12
Buffer Tube Material:	Thermoplastic

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Strength Member

Strength Member Material:	Aramid Yarn
----------------------------------	-------------

Armor

Armor Type:	Interlocked
Armor Material:	Aluminum

Overall Cable

Overall Nominal Diameter:	0.620 in.
----------------------------------	-----------

Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +75°C
Installation Temperature Range:	0°C To +75°C
Operating Temperature Range:	0°C To +75°C
Bulk Cable Weight:	149 lbs/1000 ft.
Min. Bend Radius (Install)/Minor Axis:	8.400 in.
Min. Bend Radius for Long Term Application:	6 in.
Max. Load for Installation:	239 lbs.
Max. Load for Long Term Application:	119 lbs.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	OFCR
CEC/C(UL) Specification:	OFC
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/01/2008
EU Directive 2002/96/EC (WEEE):	Yes

B9C231 Fiber - Industrial Armored Cable - Riser

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1666 Riser

CSA Flame Test: FT4

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: No

Suitability - Aerial: No

Suitability - Burial: No

Sunlight Resistance: No

Plenum/Non-Plenum

Plenum (Y/N): No

Optical Characteristics (Overall)

Maximum Attenuation @ 850nm: 3.0 dB/km

Maximum Attenuation @ 1300nm: 1.2 dB/km

Minimum Bandwidth @ 850nm: 1500 MHz*km

Minimum Bandwidth @ 1300nm: 500 MHz*km

Maximum Gigabit Ethernet Length @ 850nm: 1000

Maximum Gigabit Ethernet Length @ 1300nm: 550

Fiber Coding MLT EMEA:

Fiber/Tube No.	Color
1	Blue
2	Orange
3	Green
4	Brown
5	Gray
6	White
7	Red
8	Black
9	Yellow
10	Purple
11	Rose
12	Aqua

Related Documents:

[DOUBLE JACKETED INTERLOCKED ARMOR DISTRIBUTION CABLE.pdf](#) - Document PG 46 - DOUBLE JACKETED INTERLOCKED ARMOR DISTRIBUTION CABLE rev 8.pdf

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
B9C231	1 FT	0.170 LB	AQUA		12G5 DIST IARM RSR AQU

Revision Number: 1 Revision Date: 07-12-2010

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express,

B9C231 Fiber - Industrial Armored Cable - Riser

statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.