


AX101873 Panels - MediaFlex Surface Adapter Box Double Gang

For more Information
please call

1-800-Belden1

**Description:**

MediaFlex Surface Adapter Box Double Gang

Usage (Overall)

Suitable Applications:	- Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400, 1200, Fiber and Coax.
Related Parts:	Compatible with MediaFlex Plates

Physical Characteristics (Connectivity)**Dimensions**

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
4.620	5.300	1.750

Materials

Materials:

Description	Material
Adapter Box	Plastic - UL94V-0

Color

Color: Gray

Included Parts

Included Parts: adhesive foam tape, installation guide

Packaging

Packaging: Individually shrink wrapped with plastic

Mechanical Characteristics (Connectivity)

Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
MII Order #39 (China RoHS):	Yes
Safety Listing:	ACA, Bi-national (UL/CSA) Standard Listed

Suitability

Suitability - Indoor: Yes

Notes (Overall)

Notes: For proper installation refer to Installation Guide PX102064 included with the product or visit our web site at <http://www.belden.com>

AX101873 Panels - MediaFlex Surface Adapter Box Double Gang**Product Family****Part Numbers:**

Description	Gray	Almond	Elec. White	Black	White	Ivory
MediaFlex Surface Adapter Boxes Single Gang	AX102480	AX102481	AX102482	AX102483	AX102484	AX102485
MediaFlex Surface Adapter Boxes Double Gang	AX101873	AX101874	AX101875	AX101876	AX102610	AX102571

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX101873	1 EA	0.172 LB			MEDIAFLEX DOUBLE GANG AD

Revision Number: 0 Revision Date: 05-28-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.