



End-of-line terminator

Leader cable

J-clips

Caution tag



SeaHawk

Cable Installation Accessories

RLE provides accessories to make the installation of leak detection cable (sensing cable) easy and complete. These cable installation accessories include:

Leader cable and end-of-line (EOL) terminator

The 15-foot (4.57m) leader cable achieves easy connectivity with any SeaHawk leak detection controller. The EOL terminator connects to the end of the sensing cable to provide a complete circuit in a leak detection system. These two parts are necessary components for any SeaHawk leak detection system and are sold with most SeaHawk leak detection controllers. They are also sold together as a Leader Cable Kit (LC-KIT) or as individual components.

J-Clips

J-clips help prevent cable from shifting after installation and can be used with SeaHawk sensing cable or non-sensing cable. J-clips are constructed of durable nylon with a self-adhesive backing for easy installation.

Caution labels

Fluorescent, adhesive tags clearly mark the location of sensing cable or non-sensing cable. As required, wrap the tags around any exposed cable at ten-foot intervals and use the space provided on each tag to note the distance from the leak detection controller or the length of the cable.

Accessories

- Leader cable
- End-of-line (EOL) terminator
- J-Clips
- Caution tags

Note: The leader cable and EOL terminator are also sold together as a Leader Cable Kit (LC-Kit) or as individual components.

Leak Detection

www.rletech.com

Cable Installation Accessories Specifications

Leader Cable and End-of-Line (EOL) Terminator

Specification	Leader Cable	End-of-Line (EOL) Terminator
Connections	22 AWG NO Conductors 4 Nom. Insul. Thick .006 in. (.01524cm) Nom. Jacket Thick 0.010 in. (.0254cm) Nom O.D. 0.121 in. (.307cm) Lbs/M 14 Compatible with SeaHawk sensing cable (not included) AMP 4-pin circular receptacle	22 AWG NO Conductors 4 Nom. Insul. Thick .006 in. (.01524cm) Nom. Jacket Thick 0.010 in. (.0254cm) Nom O.D. 0.121 in. (.307cm) Lbs/M 14 Compatible with SeaHawk sensing cable (not included) AMP 4-pin circular receptacle
Standards	NEC Article 725-CL2P,CMP, MPP	NEC Article 725-CL2P,CMP, MPP
Operating Environment Temperature Humidity Altitude	32° to 122°F (0° to 50°C) 5% to 95% RH, non-condensing 15,000ft (4,572m) max.	32° to 122°F (0° to 50°C) 5% to 95% RH, non-condensing 15,000ft (4,572m) max.
Storage Environment	-4° to 158°F (-20° to 70°C)	-4° to 158°F (-20° to 70°C)
Length or Dimensions	15 ft. (4.57m)	2.0"L x 0.9"W (50.8mmL x 22.9mmW)
Weight	.232 oz. (6.6g)	0.4 oz. (11.3g)
Certifications	Pending	Pending

J-Clip

Material	White, UL94 V-1, RMS-05 nylon
Operating Environment (adhesive tape temperature)	-4 to 122°F (-20 to 50°C)
Dimensions	1"W x 1.1"H x 0.5"D (25mmW x 28mmH x 12mmD)
Certifications	n/a



Although the information contained in this document is believed to be accurate and correct, RLE Technologies assumes no responsibility, and disclaims all liability, for any damages resulting from the use of this information or any error or omission in this document. RLE Technologies does not warrant, guarantee, or make any representations as to the performance, fitness for use, safety, or reliability of any existing or future wiring, equipment, additions or modifications to equipment, or any other component of the original or modified system. Specifications are subject to change without notice.

110080 Rev 1.0 (6/2010) ©2010 RLE Technologies



104 Racquette Drive
Fort Collins, CO 80524
970.484.6510
www.rletech.com