

AX103914 Panels - FiberExpress Ultra Splice Tray 12 inches



For more Information
please call

1-800-Belden1



Description:

FiberExpress Ultra 12 inches Splice Tray

Usage (Overall)

Suitable Applications: FiberExpress Ultra Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Related Parts: FiberExpress Ultra 1U Patch Panels And Rack Mount Splice Enclosure

Physical Characteristics (Connectivity)

Capacity

Max. Capacity: Optimal 24 Splices

Dimensions

Dimensions:

Height (in.)	Width (in.)	Length (in.)
0.550	5.500	12.000

Materials

Materials:

Description	Material	Color
Splice Tray	Metal	Black

Weight

Weight: 1.100 lbs.

Packaging

Packaging: Individually packaged in a plastic bag, Shipped in cardboard box (20/box)

Mechanical Characteristics (Connectivity)

Storage Temperature Range: -40°C To +80°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2006

Suitability

Suitability - Indoor: Yes

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For additional information about this product refer to product buletin NP286, or visit our web site at <http://www.belden.com>.

Product Family

Part Numbers:

Description	Item Number
FiberExpress Ultra Splice Tray 8 inches	AX103912

AX103914 Panels - FiberExpress Ultra Splice Tray 12 inches

FiberExpress Ultra Splice Tray 10 inches	AX103913
FiberExpress Ultra Splice Tray 12 inches	AX103914

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 0 Revision Date: 09-11-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.