


RiserLite® Loose Tube

Indoor/Outdoor
UL/c(UL) Type OFNR/OFN FT4

DESCRIPTION

RISERLITE INDOOR/OUTDOOR LOOSE TUBE FIBER OPTIC CABLE IS A DRY CORE CABLE WITH MOISTURE BLOCKING GEL INSIDE THE THERMOPLASTIC BUFFER TUBE. THE INDIVIDUALLY COLORED 250 μ m FIBERS ARE SURROUNDED BY GEL FOR MOISTURE RESISTANCE. EACH INDIVIDUAL 6 OR 12 FIBER GROUP IS PROTECTED WITH A COLORED PBT TUBE AND CABLED AROUND A RIGID EPOXY FIBERGLASS CENTRAL STRENGTH MEMBER WHICH PROVIDES SUPERIOR PROTECTION AGAINST THERMAL EXPANSION AND CONTRACTION OVER THE OPERATING TEMPERATURE RANGE. AN OVERALL WATER-SWELLABLE TAPE PROVIDES AXIAL WATER PENETRATION PROTECTION. THE CORE IS HELICALLY WRAPPED WITH ARAMID YARN FOR TENSILE STRENGTH AND PROTECTED WITH AN OVERALL BLACK FLAME AND UV RESISTANT THERMOPLASTIC JACKET WHICH MEETS ALL THE REQUIREMENTS OF UL/cUL TYPE OFNR, OFN FT4 FLAME RATINGS. MOHAWK'S RISERLITE FIBER CABLES ARE OFFERED IN ALL GRADES OF MULTIMODE AND SINGLE-MODE UP TO 144 FIBERS.



PRODUCT FEATURES/BENEFITS

- NO SPLICING REQUIRED AT BUILDING ENTRANCE
- AVAILABLE WITH ZERO-HALOGEN JACKET
- BREAKOUT KITS AVAILABLE
- FULLY WATERBLOCKED

APPLICATIONS

- INDOOR/OUTDOOR INSTALLATIONS
- TELECOMMUNICATIONS AND DATA TRUNK
- BUILDING INTERCONNECTIONS
- DUCTS BETWEEN BUILDINGS

MECHANICAL & ENVIRONMENTAL CHARACTERISTICS

• CRUSH RESISTANCE	(EIA-455-41)	2000 N/cm
• IMPACT RESISTANCE	(EIA-455-25)	2000 IMPACTS W/1.6 N-m
• MIN. BEND RADIUS	LONG TERM-NO LOAD	15X CABLE DIAMETER
• MIN. BEND RADIUS	SHORT TERM-LOAD	20X CABLE DIAMETER
• OPERATING TEMP.	--	-40°C TO +70°C
• INSTALLATION TEMP.	--	-20°C TO +60°C
• STORAGE TEMP.	--	-40°C TO +80°C
• UL/C(UL) RATED	TYPE OFNR/OFN FT4	
• FLAME RESISTANCE	UL 1666	PASSED

RiserLite® Loose Tube

Indoor/Outdoor
UL/c(UL) Type OFNR/OFN FT4

Part Number	Fiber Count	Fibers Per Tube	Outside Diameter		Weight		Min. Bend Radius				Max. Load (Installation)	
			mm	in.	kg/km	lbs/M'	Short Term		Long Term		Newtons	lbs.
M9X810	6	6	9.65	.380	94	63	19.3	7.6	14.5	5.7	2700	600
M9X811	12	6	9.65	.380	92	62	19.3	7.6	14.5	5.7	2700	600
M9X812	24	6	9.65	.380	91	61	19.3	7.6	14.5	5.7	2700	600
M9X813	36	6	9.65	.380	89	60	19.3	7.6	14.5	5.7	2700	600
M9X814	48	12	12.19	.480	132	89	24.4	9.6	18.3	7.2	2700	600
M9X815	72	12	12.19	.480	129	87	24.4	9.6	18.3	7.2	2700	600
M9X816	96	12	13.89	.547	170	114	27.7	10.9	20.8	8.2	2700	600
M9X817	144	12	17.78	.700	278	187	35.6	14.0	26.7	10.5	2700	600

For "X" in part number see optical characteristics below.

Optical Characteristics

Meets or exceeds ISO/IEC 11801

	OM1	OM1	OM2	OM3	OM3	
Grade	2	3	4	5	6	SM2
Glass Type	62.5/125 MM AdvanceLite	62.5/125 MM AdvanceLite	50/125 MM AdvanceLite	50/125 MM AdvanceLite	50/125 MM AdvanceLite	Single-Mode Enhanced ⁵
Part Number Code (X)	B	D	A	C	E	W
Operating Wavelength (nm)	850/1300	850/1300	850/1300	850/1300	850/1300	1310/1550
Min. OFL ¹ Bandwidth (MHz-km)	200/500	200/500	500/500	1500/500	3000/500	—
Min. Laser ² Bandwidth (MHz-km)	220/500	385/500	510/500	2000/500	4700/500	—
Max. Attenuation RiserLite (dB/km)	3.50/1.25	3.50/1.25	3.50/1.25	3.50/1.25	3.50/1.25	0.80/0.50
100 Mbit Fast Ethernet Min. Link Length (meters S/L/E ³)	300/2000	300/2000	300/2000	300/2000	300/2000	5000/—
1 Gigabit Ethernet Min. Link Length (meters S/L/E ³)	300/550	500/1000	600/600	1000 ⁴ /600	1000 ⁴ /600	5000/—
10 Gigabit Ethernet Min. Link Length (meters S/L/E ³)	33/300	33/300	82/300	300/300	550/300	10,000/40,000

¹ OFL – Overfilled Launch

² Effective Modal Bandwidth, determined by RML or DMD performance specifications

³ S/L/E – Short wavelength (850 nm) / Long wavelength (1310 nm) / Extra long wavelength (1550 nm)

⁴ >2000 meters for engineered links

⁵ Low water peak Single-Mode suitable for CWDM use complies with ITU G.652.c/d

Mohawk reserves the right to change specification in the interest of product enhancement.

MOHAWK

9 Mohawk Drive, Leominster, MA 01453
(978) 537-9961 • 1-800-422-9961 • FAX (978) 537-4358
info@mohawk-cable.com www.mohawk-cable.com