


I601255 Fiber - TrayOptic®



For more Information
please call

1-800-Belden1



Description:

All TrayOptic® cables have been upgraded with a water-blocking agent. The TrayOptic series of products utilize the LCF™ to handle tomorrow's gigabit Ethernet light sources and expanded bandwidth requirements.

Physical Characteristics (Overall)

Fiber Type:	62.5/125/250 Micron
Number of Fibers:	12
Core Diameter:	62.5 +/- 2.5
Core Non-Circularity:	5% Maximum
Clad Diameter:	125 +/- 2
Clad Non-Circularity:	1% Maximum
Primary Coating Material:	Acrylate
Primary Coating Diameter:	245 +/- 10

Fiber Color Code Chart:

Color
Blue, Orange
Green
Brown
Gray
White

Buffer Tube Diameter:	1.9
Buffer Tube Material:	Flame Retardant Thermoplastic
Buffer Tube Filling Material:	Synthetic Thixotropic Gel

Buffer Tube Color Code Chart:

Number	Color
1	Blue
2	Orange

Core-clad Offset:	1.5 Microns Maximum
--------------------------	---------------------

Inner Jacket

Inner Jacket Ripcord:	Polyester
------------------------------	-----------

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Ripcord:	Polyester
Outer Jacket Color:	Orange

Strength Member

Strength Member Material:	Fiberglass Epoxy Rod, Aramid Yarn
----------------------------------	-----------------------------------

Overall Cable

Overall Cabling Fillers:	PVC
Overall Nominal Diameter:	0.440 in.

Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +80°C
Operating Temperature Range:	-40°C To +70°C
Bulk Cable Weight:	88 lbs/1000 ft.
Min. Bend Radius (Install)/Minor Axis:	8.800 in.
Min. Bend Radius for Long Term Application:	6.600 in.
Crush Resistance:	Passes TIA/EIA 455-41; 2000 N/cm
Impact Resistance:	Passes TIA/EIA 455-25; 2000 Impacts @ 1.6 N-m
Solar Radiation Resistance:	High
Water Penetration:	Passes TIA/EIA 455-82
Compound Flow:	Passes TIA/EIA 455-81
Max. Load for Installation:	600 lbs.
Max. Load for Long Term Application:	180 lbs.
Proof Test:	100 kpsi

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	OFNR
CEC/C(UL) Specification:	OFNR
IEEE Specification:	802.3Z
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2006
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Flame Test

CSA Flame Test:	FT4
IEEE Flame Test:	1202, IEEE 383 Vertical Tray Flame Test (70,000 BTU)

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Optical Characteristics (Overall)

Maximum Attenuation @ 850nm:	3.25 dB/km
Maximum Attenuation @ 1300nm:	1.0 dB/km
Point Loss @ 850nm & 1300nm:	0.2
Minimum Bandwidth @ 850nm:	200 MHz*km
Minimum Bandwidth @ 1300nm:	500 MHz*km
Refractive Index @ 850nm:	1.496
Refractive Index @ 1300nm:	1.491

Numerical Aperture:	.275
Maximum Gigabit Ethernet Length @ 850nm:	300
Maximum Gigabit Ethernet Length @ 1300nm:	550

Related Documents:[Loose Tube Trayoptic Cable.pdf](#) - Loose Tube Trayoptic Cable**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
I601255	1 FT	0.103 LB	ORANGE		T-OPT OM1 12F OFNR LT
I601255 003X	1 FT	0.000 LB	ORANGE		REPLACED BY I601255

Revision Number: 3 Revision Date: 03-18-2009

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.