

19-INCH LCD MONITOR

- 1280 x 1024 Resolution
- Bright 300 cd/m² display
- VGA inputs
- 2x Looped BNC Inputs
- Desk stand included



SPECIFICATIONS

19-Inch CCTV LCD Monitor		Part Number - SM19P-B
Display	Screen Size	19"
	Aspect Ratio	4:3
	Resolution	1280 x 1024
	Brightness (cd/m ²)	300
	Response Time	8 ms
	Viewing Angle (H/V)	170° / 170°
	Contrast Ratio	800:1
	Pixel Pitch	0.294 x 0.294 mm
Interface	Inputs	VGA, S-Video
	Composite Inputs / Outputs (BNC)	2 / 2
Audio	Audio Input	1/8" Phono Jack
	Audio Output(s)	2 x RCA Out (L/R)
Power	Power Consumption	< 48W
Design Features	Features - PIP - 1 composite, 1 digital	Yes
	Wall Mount Hole Pattern	100 x 100 mm, Stand Included
	Remote	Included
	Power Supply	Included adapter: 12VDC, 4.0A
	Connector Location / Secured	Bottom / No
Standards	Approvals	CE, FCC, RoHS
Dimensions	Dimensions w/o stand (H/W/D)	16.5 x 13.5 x 2.5 in (419.1 x 342.9 x 63.5 mm)
Weight	Monitor Weight	10.2 lbs (4.6kg)