






- Side or rear conduit entry holes
- Outdoor rated enclosure designed to meet (IP66)
- Endures the Equivalent of 120lbs of Force
- 540TVL Color, True Day/Night, or WDR Camera Models with UTP option
- 3-Axis Mounting Bracket
- Cast Aluminum Alloy Housing
- 4-in (101mm) Polycarbonate Dome

## MLA Vandal Resistant Dome



## MLA Series

The Aigis MLA series CCTV camera housings offer a vandal resistant solution for indoor or outdoor security applications. These models include a camera and varifocal lens in a cast Aluminum housing (with the strength of 10 gauge steel) and polycarbonate dome.


All units are designed with the installer in mind: the domes are dual voltage (12VDC / 24VAC), a test monitor connection is provided inside the dome (BNC jack), two conduit entry holes are provided (side and top), the domes' two piece construction is easy to install, and the 3-axis camera bracket can be oriented in any direction.

UTP versions are available. Mounting accessories include a pendant mount with ceiling flange and a wall arm. The wall arm can be used with the MT9213 adapter to mount to a pole.

# SPECIFICATIONS

CAMERA SPECIFICATIONS			
Model No.	MLA2DN211	MLA2CH211	MLA2WD211
Description	True Day/Night Camera	Color Hi-Res Camera	Wide Dynamic Range Camera
Imager	1/3" Sony Super HAD II CCD	1/3" Sony CCD	1/3" Pixim DPS Sensor
Signal System	NTSC		
Effective Pixels	768 (H) x 494 (V)		720 (H) x 480 (V)
Resolution	540TVL		
Minimum Illumination	0.3Lux/F1.2 (Color) 0.008Lux/F1.2 (B/W)	0.1Lux/F1.2	0.5Lux/F1.2; 0.08Lux/F1.2 (Slow Shutter)
S/N Ratio	>50dB (AGC Off)	>50dB	>50dB
Dynamic Range	-		101dB Typical, 120dB Max
Control Method	-		OSD + Dipswitch
Privacy Masking	-		12 zones (optional)
Day/Night Function	Mechanical IR Cut Filter	-	Electronic D/N
Lens	2.8-11mm Auto-Iris		
White Balance	Auto	Auto	AWB/ATW/Manual Selectable
AWB Range	-		ATW 2,000K to 11,000K
BLC	Auto		-
AGC	Auto	Auto	Adjustable
Gamma Correction	-		Adjustable
Sync Mode	Internal		Internal / Line Lock
Video Output	1.0Vp-p, 75 Ohm		0.8-1.5Vp-p adjustable, 75 Ohm
Power Supply	12VDC/24VAC		
Power Consumption	<4W	<3.5W	<3W

## UTP PINOUT




Pin No.	Wire Color	Pair	Utilization
1	White-Orange	2	Video Signal
2	Orange	2	Video Shield
3	White-Green	3	Data +
4	Blue	1	Power - (Neutral)
5	White-Blue	1	Power + (Line)
6	Green	3	Data -
7	White-Brown	4	Power + (Line)
8	Brown	4	Power - (Neutral)

MECHANICAL SPECIFICATIONS		
Housing	Construction	Polycarbonate dome (clear) and cast aluminum housing.
	Finish	Standard: Powder coated white finish. Custom finishes available.
	Weight	Unit Weight - 3.3 lbs (1.5kg) / Packaged Weight - 4.2 lbs
Cable Entry		3/4-inch conduit knockout through side or back
Mounting	Surface Mount	Mounts on wall or ceiling using up to four #10 screws.
ENVIRONMENTAL		
Operating Temperature		-4 °F to +122 °F (-20 °C to +50 °C)
Humidity		0% to 90% relative, noncondensing.
Protection Level		Designed to meet IP 66.
Agency Approvals		UL, cUL

MODEL NUMBERS AND DESCRIPTIONS	
MLA2CH211	Indoor/outdoor vandal resistant dome, color high-resolution camera, 2.8-11mm varifocal AI/IR lens, 12VDC/24VAC
MLA2WD211	Indoor/outdoor vandal resistant dome, Wide Dynamic Range camera, 2.8-11mm varifocal AI/IR lens, 12VDC/24VAC
MLA2DN211	Indoor/outdoor vandal resistant dome, Day/Night camera mechanical IR cut-filter, 2.8-11mm varifocal AI/IR lens, 12VDC/24VAC
MLA2CH211-U	Same as MLA2CH211 above, except includes UTP converter
MLA2WD211-U	Same as MLA2WD211 above, except includes UTP converter
MLA2DN211-U	Same as MLA2DN211 above, except includes UTP converter

#### MLA SERIES - DIMENSIONAL DRAWING



## ACCESSORIES

Standard color is white. Stainless steel finish and custom colors available.

Mounting Kits  
for MLA Series


**MLAP**

Pipe mounting kit. Includes ceiling flange, gasket and mounting cap with screws.


**MLAW**

Wall mounting kit. Includes pendant wall mount, screws and mounting cap with screws, sealing gaskets, and pull seals.

### MLAP - MLA PIPE MOUNT ACCESSORY



### MLA-WM - MLA WALL MOUNT ACCESSORY



Accessory for the MLA: **MT9213 Pole Mount Adapter**

**aigis**  
mechtronics  
Now Part of **Linear**<sup>®</sup>  
*Building On Innovation.*

1950 Camino Vida Roble, Suite 150

Carlsbad, CA 92008

Tel: 760.438.7000 800.421.1587

www.aigismech.com • www.linearcorp.com