


760018895 | P-144-DS-8W-FMUYL
Plenum Distribution Cable, 144 fiber multi-unit with 12 fiber subunits

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber
Total Fiber Quantity	144
Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Fiber Type, quantity	144
Fibers Per Subunit, quantity	12
Jacket Color	Yellow

Dimensions

Buffer Tube/Subunit Diameter	5.90 mm 0.23 in
Cable Weight	357.0 lb/kft 531.0 kg/km
Diameter Over Jacket	24.80 mm 0.98 in
Subunit, quantity	12

Physical Specifications

Minimum Bend Radius, loaded	37.1 cm 14.6 in
Minimum Bend Radius, unloaded	24.8 cm 9.8 in
Tensile Load, long term, maximum	1335 N 300 lbf

760018895 | P-144-DS-8W-FMUYL

Tensile Load, short term, maximum 1000 lbf | 4450 N
Vertical Rise, maximum 256.0 m | 839.9 ft

Flame Test Specifications

Flame Test Listing	NEC OFNP (ETL) and c(ETL)
Flame Test Method	NFPA 262

Environmental Specifications

Environmental Space	Plenum
Installation Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression	10 N/mm 57 lb/in
Compression Test Method	FOTP-41 IEC 60794-1-2, Section 7
Flex	100 cycles
Flex Test Method	FOTP-104 IEC 60794-1-2, Section 10
Impact	4.34 ft lb 5.88 N-m
Impact Test Method	FOTP-25 IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1-2, Section 11

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-28 IEC 60794-1-2, Section 28
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596-2001 Telcordia GR-409-CORE Issue 2
-------------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



760018895 | P-144-DS-8W-FMUYL

Included Products

CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber