


760127878 | P-024-DZ-5M-FSUAQ

Plenum Distribution Cable, interlocking aluminum armored with plenum jacket, 24 fiber single-unit

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	LazrSPEED® 150, 50 µm multimode fiber
Total Fiber Quantity	24
Armor Type	Interlocking aluminum
Fiber Type	LazrSPEED® 150, 50 µm multimode fiber
Fiber Type, quantity	24
Jacket Color	Aqua

Dimensions

Cable Weight	206.0 lb/kft   307.0 kg/km
Diameter Over Armor	13.34 mm   0.53 in
Diameter Over Jacket	17.40 mm   0.69 in

Physical Specifications

Minimum Bend Radius, loaded	34.8 cm   13.7 in
Minimum Bend Radius, unloaded	24.4 cm   9.6 in
Tensile Load, long term, maximum	400 N   90 lbf

760127878 | P-024-DZ-5M-FSUAQ

Tensile Load, short term, maximum 1335 N | 300 lbf  
Vertical Rise, maximum 133.0 m | 436.4 ft

## Flame Test Specifications

Flame Test Listing	NEC OFCP (ETL) and c(ETL)
Flame Test Method	NFPA 262

## Environmental Specifications

Environmental Space	Plenum
Installation Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## Mechanical Test Specifications

Compression	485 lb/in   85 N/mm
Compression Test Method	FOTP-41   IEC 60794-1-2, Section 7
Flex	25 cycles
Flex Test Method	FOTP-104   IEC 60794-1-2, Section 10
Impact	25.80 ft lb   35.00 N-m
Impact Test Method	FOTP-25   IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1-2, Section 11

## Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-28   IEC 60794-1-2, Section 28
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1-2, Section 22

## Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596-2001   Telcordia GR-409-CORE Issue 2
-------------------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

---

CS-5M-TB (Product Component—not orderable) — LazrSPEED® 150 OM2+ Multimode Fiber