


760127738 | P-048-DZ-5M-FMUAQ

Plenum Distribution Cable, interlocking aluminum armored with plenum jacket, 48 fiber multi-unit with 12 fiber subunits

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	LazrSPEED® 150, 50 µm multimode fiber
Total Fiber Quantity	48
Armor Type	Interlocking aluminum
Fiber Type	LazrSPEED® 150, 50 µm multimode fiber
Fiber Type, quantity	48
Fibers Per Subunit, quantity	12
Jacket Color	Aqua

Dimensions

Buffer Tube/Subunit Diameter	5.90 mm 0.23 in
Cable Weight	302.0 lb/kft 449.0 kg/km
Diameter Over Armor	20.96 mm 0.83 in
Diameter Over Jacket	23.00 mm 0.91 in
Subunit, quantity	4

Physical Specifications

760127738 | P-048-DZ-5M-FMUAQ

Minimum Bend Radius, loaded	46.0 cm		18.1 in
Minimum Bend Radius, unloaded	32.2 cm		12.7 in
Tensile Load, long term, maximum	400 N		90 lbf
Tensile Load, short term, maximum	1335 N		300 lbf
Vertical Rise, maximum	91.0 m		298.6 ft

Flame Test Specifications

Flame Test Listing	NEC OFCP (ETL) and c(ETL)
Flame Test Method	NFPA 262

Environmental Specifications

Environmental Space	Plenum
Installation Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression	485 lb/in		85 N/mm
Compression Test Method	FOTP-41		IEC 60794-1-2, Section 7
Flex	25 cycles		
Flex Test Method	FOTP-104		IEC 60794-1-2, Section 10
Impact	25.80 ft lb		35.00 N-m
Impact Test Method	FOTP-25		IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads		
Strain Test Method	FOTP-33		IEC 60794-1-2, Section 5
Twist	10 cycles		
Twist Test Method	FOTP-85		IEC 60794-1-2, Section 11

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-28 IEC 60794-1-2, Section 28
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596-2001 Telcordia GR-409-CORE Issue 2
-------------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5M-TB (Product Component—not orderable) — LazrSPEED® 150 OM2+ Multimode Fiber