


760018515 | R-024-DS-8W-FSUYL
Riser Distribution Cable, 24 fiber single-unit

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber
Total Fiber Quantity	24
Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Fiber Type, quantity	24
Jacket Color	Yellow

Dimensions

Cable Weight	38.0 lb/kft 56.0 kg/km
Diameter Over Jacket	8.40 mm 0.33 in

Physical Specifications

Minimum Bend Radius, loaded	12.5 cm 4.9 in
Minimum Bend Radius, unloaded	8.4 cm 3.3 in
Tensile Load, long term, maximum	400 N 90 lbf
Tensile Load, short term, maximum	1335 N 300 lbf

760018515 | R-024-DS-8W-FSUYL

Vertical Rise, maximum 500.0 m | 1640.4 ft

Flame Test Specifications

Flame Test Listing	NEC OFNR (ETL) and c(ETL)
Flame Test Method	UL 1666

Environmental Specifications

Environmental Space	Riser
Installation Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression	10 N/mm 57 lb/in
Compression Test Method	FOTP-41 IEC 60794-1-2, Section 7
Flex	100 cycles
Flex Test Method	FOTP-104 IEC 60794-1-2, Section 10
Impact	4.34 ft lb 5.88 N-m
Impact Test Method	FOTP-25 IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1-2, Section 11

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-28 IEC 60794-1-2, Section 28
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596-2001 Telcordia GR-409-CORE Issue 2
-------------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber