


700211287 | Z-024-DS-6F-FMUBK

Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 24 fiber multi-unit with 6 fiber subunits

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	OptiSPEED®, 62.5 µm multimode fiber
Total Fiber Quantity	24
Fiber Type	OptiSPEED®, 62.5 µm multimode fiber
Fiber Type, quantity	24
Fibers Per Subunit, quantity	6
Jacket Color	Black
Jacket UV Resistance	UV stabilized

Dimensions

Buffer Tube/Subunit Diameter	5.50 mm 0.22 in
Cable Weight	133.0 lb/kft 198.0 kg/km
Diameter Over Jacket	16.40 mm 0.65 in
Subunit, quantity	4

Physical Specifications

Minimum Bend Radius, loaded	24.6 cm 9.7 in
Minimum Bend Radius, unloaded	16.4 cm 6.5 in
Tensile Load, long term, maximum	180 lbf 801 N
Tensile Load, short term, maximum	600 lbf 2670 N

700211287 | Z024-DS-6FFMUBK

Vertical Rise, maximum 413.0 m | 1355.0 ft

Flame Test Specifications

Flame Test Listing	NEC OFNR-LS (ETL) and c(ETL)
Flame Test Method	IEC 60332-3 IEC 60754-2 IEC 61034-2 IEEE 383 UL 1666 UL 1685

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH) Riser
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

Mechanical Test Specifications

Compression	126 lb/in 22 N/mm
Compression Test Method	FOTP-41 IEC 60794-1-2, Section 7
Flex	100 cycles
Flex Test Method	FOTP-104 IEC 60794-1-2, Section 10
Impact	4.34 ft lb 5.88 N-m
Impact Test Method	FOTP-25 IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1-2, Section 11
Water Penetration	24 h
Water Penetration Test Method	FOTP-82 IEC 60794-1-2, Section 24

Environmental Test Specifications

Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-40 °C to +70 °C (-40 °F to +158 °F)
Low High Bend Test Method	FOTP-28 IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-104-696-2001 EN 187105 Telcordia GR -20-CORE Issue 3 (water penetration) Telcordia GR-409-CORE Issue 2
-------------------------------	--

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-6F-TB (Product Component—not orderable) — OptiSPEED® OM1 Multimode Fiber