


760026823 | R-096-DS-8W-FMUYL
Riser Distribution Cable, 96 fiber multi-unit with 12 fiber subunits

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber
Total Fiber Quantity	96
Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Fiber Type, quantity	96
Fibers Per Subunit, quantity	12
Jacket Color	Yellow

Dimensions

Buffer Tube/Subunit Diameter	6.00 mm 0.24 in
Cable Weight	337.0 lb/kft 502.0 kg/km
Diameter Over Jacket	23.70 mm 0.93 in
Subunit, quantity	8

Physical Specifications

Minimum Bend Radius, loaded	35.6 cm 14.0 in
Minimum Bend Radius, unloaded	23.7 cm 9.3 in
Tensile Load, long term, maximum	1335 N 300 lbf

760026823 | R-096-DS-8W-FMUYL

Tensile Load, short term, maximum 1000 lbf | 4450 N
Vertical Rise, maximum 271.0 m | 889.1 ft

Flame Test Specifications

Flame Test Listing NEC OFNR (ETL) and c(ETL)
Flame Test Method UL 1666

Environmental Specifications

Environmental Space Riser
Installation Temperature -20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature -20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression 10 N/mm | 57 lb/in
Compression Test Method FOTP-41 | IEC 60794-1-2, Section 7
Flex 100 cycles
Flex Test Method FOTP-104 | IEC 60794-1-2, Section 10
Impact 4.34 ft lb | 5.88 N-m
Impact Test Method FOTP-25 | IEC 60794-1-2, Section 8
Strain See long and short term tensile loads
Strain Test Method FOTP-33 | IEC 60794-1-2, Section 5
Twist 10 cycles
Twist Test Method FOTP-85 | IEC 60794-1-2, Section 11

Environmental Test Specifications

Heat Age -20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method Not applicable
Low High Bend -20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method FOTP-28 | IEC 60794-1-2, Section 28
Temperature Cycle -20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method FOTP-3 | IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards ANSI/ICEA S-83-596-2001 | Telcordia GR-409-CORE Issue 2

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



760026823 | R-096-DS-8W-FMUYL

Included Products

CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber