



760139121 | RK6-58S

**Rack, 2-Post, (58U), 6 in (152 mm) Channel x 9 ft (2743 mm) H x 19 in (482.6 mm) W, steel, 3/8 square punch, black**

## Dimensions

Channel Width	6.0 in
Depth	457.2 mm   18.0 in
Dimensional Standards	EIA-310-D
Height	2743.2 mm   108.0 in
Width	515.6 mm   20.3 in

## General Specifications

Product Type	2 post rack
Rack Units	58
Color	Black
Finish	Powder-coated, textured
Includes	Forty M6 cage nuts   Four M6 x 12 mm mounting screws   Instruction sheet   Twelve 3/8 in split lock washers   Twelve 3/8-16 hex nuts   Twelve 3/8-16 UNC x 1 in hex head bolts   Two extruded base angles   Two extruded top angles   Two vertical rack rails
Package, quantity	1
Packaging Type	Flat packed
Rack Type	EIA 19 in

## Mechanical Specifications

Rail Mounting Hole	3/8 in
Material Type	Steel
Static Load Rating	453.6 kg   1000.0 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

