


760053520 | D-024-LA-5M-F12NS  
Single Jacket Single Armor Outdoor Cable Arid-Core Construction Stranded Loose Tube

## Representative Image



## General Specifications

|                   |                     |
|-------------------|---------------------|
| Cable Type        | Stranded loose tube |
| Construction Type | Armored             |
| Subunit Type      | Gel-free            |

## Construction Materials

|                              |                                       |
|------------------------------|---------------------------------------|
| Fiber Type Solution          | LazrSPEED® 150, 50 µm multimode fiber |
| Total Fiber Quantity         | 24                                    |
| Armor Type                   | Corrugated steel                      |
| Fiber Type                   | LazrSPEED® 150, 50 µm multimode fiber |
| Fiber Type, quantity         | 24                                    |
| Fibers Per Subunit, quantity | 12                                    |
| Jacket Color                 | Black                                 |
| Jacket UV Resistance         | UV stabilized                         |

## Dimensions

|                              |                           |
|------------------------------|---------------------------|
| Buffer Tube/Subunit Diameter | 2.50 mm   0.10 in         |
| Cable Weight                 | 116.0 kg/km   78.0 lb/kft |
| Diameter Over Jacket         | 11.50 mm   0.45 in        |
| Filler, quantity             | 3                         |
| Subunit, quantity            | 2                         |

## Physical Specifications

|                             |                  |
|-----------------------------|------------------|
| Minimum Bend Radius, loaded | 17.3 cm   6.8 in |
|-----------------------------|------------------|

760053520 | D024LA-5MF12NS

|                                   |                     |
|-----------------------------------|---------------------|
| Minimum Bend Radius, unloaded     | 11.5 cm   4.5 in    |
| Tensile Load, long term, maximum  | 180 lbf   800 N     |
| Tensile Load, short term, maximum | 2700 N   607 lbf    |
| Vertical Rise, maximum            | 705.0 m   2313.0 ft |

## Environmental Specifications

|                          |                                      |
|--------------------------|--------------------------------------|
| Environmental Space      | Aerial, lashed   Buried              |
| Installation Temperature | -30 °C to +70 °C (-22 °F to +158 °F) |
| Operating Temperature    | -40 °C to +70 °C (-40 °F to +158 °F) |
| Storage Temperature      | -40 °C to +75 °C (-40 °F to +167 °F) |

## Mechanical Test Specifications

|                               |                                       |
|-------------------------------|---------------------------------------|
| Compression                   | 250 lb/in   44 N/mm                   |
| Compression Test Method       | FOTP-41   IEC 60794-1-2, Section 7    |
| Flex                          | 35 cycles                             |
| Flex Test Method              | FOTP-24   IEC 60794-1-2, Section 10   |
| Impact                        | 2.17 ft lb   2.94 N-m                 |
| Impact Test Method            | FOTP-25   IEC 60794-1-2, Section 8    |
| Strain                        | See long and short term tensile loads |
| Strain Test Method            | FOTP-33   IEC 60794-1-2, Section 5    |
| Twist                         | 10 cycles                             |
| Twist Test Method             | FOTP-85   IEC 60794-1-2, Section 11   |
| Water Penetration             | 24 h                                  |
| Water Penetration Test Method | FOTP-82   IEC 60794-1-2, Section 24   |

## Environmental Test Specifications

|                               |                                      |
|-------------------------------|--------------------------------------|
| Cable Freeze                  | -2 °C   28 °F                        |
| Cable Freeze Test Method      | FOTP-98                              |
| Heat Age                      | -40 °C to +85 °C (-40 °F to +185 °F) |
| Heat Age Test Method          | Not applicable                       |
| Low High Bend                 | -30 °C to +60 °C (-22 °F to +140 °F) |
| Low High Bend Test Method     | FOTP-28   IEC 60794-1-2, Section 28  |
| Temperature Cycle             | -40 °C to +70 °C (-40 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3   IEC 60794-1-2, Section 22   |

## Qualification Specifications

|                               |                                                                     |
|-------------------------------|---------------------------------------------------------------------|
| Cable Qualification Standards | ANSI/ICEA S-87-640-2006   EN 187105   Telcordia GR -20-CORE Issue 3 |
|-------------------------------|---------------------------------------------------------------------|

## Regulatory Compliance/Certifications

| Agency          | Classification                                                                 |
|-----------------|--------------------------------------------------------------------------------|
| RoHS 2002/95/EC | Compliant                                                                      |
| ISO 9001:2008   | Designed, manufactured and/or distributed under this quality management system |



## Included Products

---

CS-5M-LT (Product Component—not orderable) — LazrSPEED® 150 OM2+ Multimode Fiber